

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584099

Luminaire Tested: **HCC8S25D010MB-HM82555827-81MDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584099
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010MB-HM82555827-81MDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2668.5 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584099
CATALOG NUMBER: HCC8S25D010MB-HM82555827-81MDC

Luminous Intensity Polar Plot





TEST NUMBER: P584099

CATALOG NUMBER: HCC8S25D010MB-HM82555827-81MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84	84	84	84
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79	79	79	79
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75	75	75	75
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71	71	71	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67	67	67	67
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64	64	64	64
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61	61	61	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58	58	58	58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	159439
5°	152124
10°	131338
15°	100430
20°	76844
25°	60794
30°	45926
35°	24431
40°	9307
45°	4466
50°	1900
55°	801
60°	302
65°	241
70°	144
75°	0
80°	0
85°	0



TEST NUMBER: P584099
 CATALOG NUMBER: HCC8S25D010MB-HM82555827-81MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	446.1	16.7
10°-20°	878.2	32.9
20°-30°	817.9	30.7
30°-40°	422.1	15.8
40°-50°	86.0	3.2
50°-60°	14.7	0.6
60°-70°	2.8	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2142.3	80.3
0°-40°	2564.3	96.1
0°-60°	2665.0	99.9
0°-90°	2668.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2668.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5170	
5°	4914	446
15°	3146	878
25°	1787	818
35°	649	422
45°	102	86
55°	15	15
65°	3	3
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P584099
CATALOG NUMBER: HCC8S25D010MB-HM82555827-81MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	5170.5
2.5°	5101.1
5°	4914.5
7.5°	4607.4
10°	4194.5
12.5°	3652.9
15°	3145.9
17.5°	2706.7
20°	2341.7
22.5°	2044.4
25°	1786.8
27.5°	1542.4
30°	1289.8
32.5°	989.2
35°	649.0
37.5°	376.5
40°	231.2
42.5°	151.9
45°	102.4
47.5°	64.4
50°	39.6
52.5°	23.1
55°	14.9
57.5°	6.6
60°	4.9
62.5°	3.3
65°	3.3
67.5°	1.6
70°	1.6
72.5°	1.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)