

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584105

Luminaire Tested: **HCC8S25D010SL-HM82555827-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584105
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010SL-HM82555827-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2455.6 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584105
CATALOG NUMBER: HCC8S25D010SL-HM82555827-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P584105
 CATALOG NUMBER: HCC8S25D010SL-HM82555827-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89				
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79				
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71				
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64				
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58				
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53				
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49				
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45				
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42				
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	57639
5°	56887
10°	54805
15°	52659
20°	51205
25°	49665
30°	44565
35°	29216
40°	16150
45°	13467
50°	12276
55°	11720
60°	10898
65°	9879
70°	8935
75°	8066
80°	7334
85°	7005



TEST NUMBER: P584105
 CATALOG NUMBER: HCC8S25D010SL-HM82555827-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.7	7.0
10°-20°	465.4	19.0
20°-30°	662.3	27.0
30°-40°	490.2	20.0
40°-50°	242.8	9.9
50°-60°	193.8	7.9
60°-70°	134.6	5.5
70°-80°	72.5	3.0
80°-90°	21.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1300.4	53.0
0°-40°	1790.6	72.9
0°-60°	2227.2	90.7
0°-90°	2455.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2455.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1869	
5°	1838	173
15°	1650	465
25°	1460	662
35°	776	490
45°	309	243
55°	218	194
65°	135	135
75°	68	73
85°	20	21
90°	0	



TEST NUMBER: P584105
CATALOG NUMBER: HCC8S25D010SL-HM82555827-81PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1869.2
2.5°	1860.9
5°	1837.8
7.5°	1801.5
10°	1750.3
12.5°	1697.4
15°	1649.5
17.5°	1603.3
20°	1560.4
22.5°	1517.5
25°	1459.7
27.5°	1375.5
30°	1251.6
32.5°	1061.8
35°	776.1
37.5°	530.1
40°	401.2
42.5°	343.5
45°	308.8
47.5°	280.7
50°	255.9
52.5°	234.4
55°	218.0
57.5°	198.2
60°	176.7
62.5°	155.3
65°	135.4
67.5°	115.6
70°	99.1
72.5°	82.6
75°	67.7
77.5°	54.5
80°	41.3
82.5°	29.7
85°	19.8
87.5°	8.2
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)