

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584118

Luminaire Tested: **HCC8S25D010MB-HM82555830-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584118
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010MB-HM82555830-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2388.2 lumens
Efficiency: N/A
Efficacy: 89.1 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584118
CATALOG NUMBER: HCC8S25D010MB-HM82555830-81MDW

Luminous Intensity Polar Plot





TEST NUMBER: P584118

CATALOG NUMBER: HCC8S25D010MB-HM82555830-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80			80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72			72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65			65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59			59
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54			54
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50			50
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			43
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40			40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61062
5°	59401
10°	55898
15°	52924
20°	50906
25°	48940
30°	43469
35°	27680
40°	15449
45°	12939
50°	11681
55°	11010
60°	10046
65°	9055
70°	7997
75°	7113
80°	6304
85°	5732



TEST NUMBER: P584118
 CATALOG NUMBER: HCC8S25D010MB-HM82555830-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.9	7.5
10°-20°	467.5	19.6
20°-30°	652.2	27.3
30°-40°	469.3	19.7
40°-50°	232.6	9.7
50°-60°	182.0	7.6
60°-70°	123.2	5.2
70°-80°	64.0	2.7
80°-90°	18.4	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1298.7	54.4
0°-40°	1768.0	74.0
0°-60°	2182.5	91.4
0°-90°	2388.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2388.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1980	
5°	1919	179
15°	1658	468
25°	1438	652
35°	735	469
45°	297	233
55°	205	182
65°	124	123
75°	60	64
85°	16	18
90°	0	



TEST NUMBER: P584118
CATALOG NUMBER: HCC8S25D010MB-HM82555830-81MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1980.2
2.5°	1962.6
5°	1919.0
7.5°	1857.7
10°	1785.2
12.5°	1717.5
15°	1657.8
17.5°	1601.4
20°	1551.3
22.5°	1501.3
25°	1438.4
27.5°	1348.1
30°	1220.8
32.5°	1020.8
35°	735.3
37.5°	501.5
40°	383.8
42.5°	330.6
45°	296.7
47.5°	267.7
50°	243.5
52.5°	222.6
55°	204.8
57.5°	183.8
60°	162.9
62.5°	141.9
65°	124.1
67.5°	106.5
70°	88.7
72.5°	74.2
75°	59.7
77.5°	46.8
80°	35.5
82.5°	25.8
85°	16.2
87.5°	8.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)