

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584135

Luminaire Tested: **HCC8S25D010SL-HM82555835-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584135
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010SL-HM82555835-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2531.5 lumens
Efficiency: N/A
Efficacy: 94.5 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584135
CATALOG NUMBER: HCC8S25D010SL-HM82555835-81MDW

Luminous Intensity Polar Plot





TEST NUMBER: P584135

CATALOG NUMBER: HCC8S25D010SL-HM82555835-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80			80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72			72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65			65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59			59
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54			54
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50			50
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			43
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40			40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64729
5°	62967
10°	59252
15°	56100
20°	53965
25°	51880
30°	46079
35°	29344
40°	16375
45°	13719
50°	12382
55°	11672
60°	10651
65°	9602
70°	8484
75°	7530
80°	6677
85°	6050



TEST NUMBER: P584135
 CATALOG NUMBER: HCC8S25D010SL-HM82555835-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.6	7.5
10°-20°	495.6	19.6
20°-30°	691.4	27.3
30°-40°	497.5	19.7
40°-50°	246.6	9.7
50°-60°	192.9	7.6
60°-70°	130.6	5.2
70°-80°	67.8	2.7
80°-90°	19.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1376.6	54.4
0°-40°	1874.1	74.0
0°-60°	2313.6	91.4
0°-90°	2531.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2531.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2099	
5°	2034	190
15°	1757	496
25°	1525	691
35°	780	497
45°	315	247
55°	217	193
65°	132	131
75°	63	68
85°	17	20
90°	0	



TEST NUMBER: P584135
CATALOG NUMBER: HCC8S25D010SL-HM82555835-81MDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2099.1
2.5°	2080.3
5°	2034.2
7.5°	1969.2
10°	1892.3
12.5°	1820.5
15°	1757.3
17.5°	1697.4
20°	1644.5
22.5°	1591.4
25°	1524.8
27.5°	1429.1
30°	1294.1
32.5°	1082.1
35°	779.5
37.5°	531.6
40°	406.8
42.5°	350.4
45°	314.6
47.5°	283.8
50°	258.1
52.5°	235.9
55°	217.1
57.5°	194.8
60°	172.7
62.5°	150.4
65°	131.6
67.5°	112.8
70°	94.1
72.5°	78.6
75°	63.2
77.5°	49.5
80°	37.6
82.5°	27.4
85°	17.1
87.5°	8.6
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)