

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584139

Luminaire Tested: **HCC8W25D010MB-HM82555835-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584139
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W25D010MB-HM82555835-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2541.8 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584139
CATALOG NUMBER: HCC8W25D010MB-HM82555835-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P584139

CATALOG NUMBER: HCC8W25D010MB-HM82555835-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89			89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79			79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64			64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49			49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45			45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	59662
5°	58887
10°	56728
15°	54510
20°	53003
25°	51407
30°	46132
35°	30243
40°	16721
45°	13937
50°	12708
55°	12134
60°	11280
65°	10230
70°	9241
75°	8352
80°	7583
85°	7253



TEST NUMBER: P584139
 CATALOG NUMBER: HCC8W25D010MB-HM82555835-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.7	7.0
10°-20°	481.7	19.0
20°-30°	685.6	27.0
30°-40°	507.4	20.0
40°-50°	251.3	9.9
50°-60°	200.6	7.9
60°-70°	139.2	5.5
70°-80°	75.0	3.0
80°-90°	22.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1346.0	53.0
0°-40°	1853.5	72.9
0°-60°	2305.4	90.7
0°-90°	2541.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2541.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1935	
5°	1902	179
15°	1708	482
25°	1511	686
35°	803	507
45°	320	251
55°	226	201
65°	140	139
75°	70	75
85°	20	22
90°	0	



TEST NUMBER: P584139

CATALOG NUMBER: HCC8W25D010MB-HM82555835-81PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1934.8
2.5°	1926.2
5°	1902.4
7.5°	1864.7
10°	1811.7
12.5°	1757.0
15°	1707.5
17.5°	1659.6
20°	1615.2
22.5°	1570.8
25°	1510.9
27.5°	1423.7
30°	1295.6
32.5°	1099.0
35°	803.4
37.5°	548.7
40°	415.4
42.5°	355.6
45°	319.6
47.5°	290.6
50°	264.9
52.5°	242.7
55°	225.7
57.5°	205.1
60°	182.9
62.5°	160.7
65°	140.2
67.5°	119.6
70°	102.5
72.5°	85.5
75°	70.1
77.5°	56.4
80°	42.7
82.5°	30.8
85°	20.5
87.5°	8.6
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)