

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584161

Luminaire Tested: **HCC8S25D010SL-HM82555840-81WDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584161  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S25D010SL-HM82555840-81WDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2945.3 lumens  
Efficiency: N/A  
Efficacy: 109.9 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584161  
CATALOG NUMBER: HCC8S25D010SL-HM82555840-81WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P584161  
 CATALOG NUMBER: HCC8S25D010SL-HM82555840-81WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93		92
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85		83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77		75
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70		68
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64		62
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58		57
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54		52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49		48
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46		44
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42		41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	67433
5°	65911
10°	63892
15°	62600
20°	62037
25°	61107
30°	57886
35°	48094
40°	28323
45°	18734
50°	14747
55°	10849
60°	7536
65°	4589
70°	2011
75°	882
80°	657
85°	0



TEST NUMBER: P584161  
 CATALOG NUMBER: HCC8S25D010SL-HM82555840-81WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	200.5	6.8
10°-20°	554.4	18.8
20°-30°	821.3	27.9
30°-40°	758.9	25.8
40°-50°	349.9	11.9
50°-60°	184.0	6.2
60°-70°	65.0	2.2
70°-80°	10.2	0.3
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1576.2	53.5
0°-40°	2335.1	79.3
0°-60°	2869.1	97.4
0°-90°	2945.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2945.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2187	
5°	2129	201
15°	1961	554
25°	1796	821
35°	1278	759
45°	430	350
55°	202	184
65°	63	65
75°	7	10
85°	0	1
90°	0	



TEST NUMBER: P584161  
CATALOG NUMBER: HCC8S25D010SL-HM82555840-81WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2186.8
2.5°	2168.2
5°	2129.3
7.5°	2086.7
10°	2040.5
12.5°	1996.0
15°	1960.9
17.5°	1929.3
20°	1890.5
22.5°	1847.9
25°	1796.0
27.5°	1725.7
30°	1625.7
32.5°	1483.1
35°	1277.6
37.5°	981.3
40°	703.6
42.5°	527.7
45°	429.6
47.5°	364.8
50°	307.4
52.5°	251.8
55°	201.8
57.5°	159.2
60°	122.2
62.5°	92.6
65°	62.9
67.5°	37.0
70°	22.3
72.5°	12.9
75°	7.4
77.5°	5.6
80°	3.7
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)