

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593619

Luminaire Tested: **HCC8S25D010BZ-HM82555850-81WDWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593619
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010BZ-HM82555850-81WDWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3049.0 lumens
Efficiency: N/A
Efficacy: 113.8 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593619
CATALOG NUMBER: HCC8S25D010BZ-HM82555850-81WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P593619
 CATALOG NUMBER: HCC8S25D010BZ-HM82555850-81WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53547
5°	53179
10°	53039
15°	54431
20°	58930
25°	63179
30°	61767
35°	51433
40°	31599
45°	21879
50°	16699
55°	10946
60°	6852
65°	5129
70°	5175
75°	5957
80°	6570
85°	5909



TEST NUMBER: P593619
 CATALOG NUMBER: HCC8S25D010BZ-HM82555850-81WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.2	5.4
10°-20°	489.5	16.1
20°-30°	842.6	27.6
30°-40°	816.4	26.8
40°-50°	402.1	13.2
50°-60°	189.7	6.2
60°-70°	74.8	2.5
70°-80°	51.6	1.7
80°-90°	19.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1495.3	49.0
0°-40°	2311.7	75.8
0°-60°	2903.5	95.2
0°-90°	3049.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3049.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1736	
5°	1718	163
15°	1705	489
25°	1857	843
35°	1366	816
45°	502	402
55°	204	190
65°	70	75
75°	50	52
85°	17	19
90°	0	



TEST NUMBER: P593619
CATALOG NUMBER: HCC8S25D010BZ-HM82555850-81WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1736.5
2.5°	1730.9
5°	1718.0
7.5°	1705.0
10°	1693.9
12.5°	1692.1
15°	1705.0
17.5°	1743.9
20°	1795.8
22.5°	1842.0
25°	1856.9
27.5°	1823.5
30°	1734.7
32.5°	1588.4
35°	1366.3
37.5°	1060.8
40°	785.0
42.5°	609.0
45°	501.7
47.5°	422.1
50°	348.1
52.5°	274.0
55°	203.6
57.5°	148.1
60°	111.1
62.5°	87.0
65°	70.3
67.5°	61.1
70°	57.4
72.5°	53.7
75°	50.0
77.5°	44.4
80°	37.0
82.5°	27.8
85°	16.7
87.5°	7.4
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)