

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584176

Luminaire Tested: **HCC8S25D010MB-HM82555927-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584176
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010MB-HM82555927-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1994.4 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584176
CATALOG NUMBER: HCC8S25D010MB-HM82555927-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P584176

CATALOG NUMBER: HCC8S25D010MB-HM82555927-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92		
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83		
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75		
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68		
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62		
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56		
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51		
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47		
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43		
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	37371
5°	37058
10°	36569
15°	36987
20°	39943
25°	43680
30°	43152
35°	35792
40°	21065
45°	13767
50°	10664
55°	7086
60°	3454
65°	1073
70°	361
75°	322
80°	231
85°	460



TEST NUMBER: P584176
 CATALOG NUMBER: HCC8S25D010MB-HM82555927-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.4	5.7
10°-20°	332.9	16.7
20°-30°	582.0	29.2
30°-40°	566.1	28.4
40°-50°	257.4	12.9
50°-60°	119.3	6.0
60°-70°	20.0	1.0
70°-80°	2.5	0.1
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1028.2	51.6
0°-40°	1594.3	79.9
0°-60°	1971.1	98.8
0°-90°	1994.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1994.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1212	
5°	1197	113
15°	1159	333
25°	1284	582
35°	951	566
45°	316	257
55°	132	119
65°	15	20
75°	3	2
85°	1	1
90°	0	



TEST NUMBER: P584176
CATALOG NUMBER: HCC8S25D010MB-HM82555927-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1211.9
2.5°	1209.2
5°	1197.2
7.5°	1183.8
10°	1167.9
12.5°	1155.9
15°	1158.6
17.5°	1179.9
20°	1217.2
22.5°	1259.8
25°	1283.8
27.5°	1270.4
30°	1211.9
32.5°	1109.3
35°	950.8
37.5°	732.4
40°	523.3
42.5°	390.2
45°	315.7
47.5°	266.3
50°	222.3
52.5°	177.1
55°	131.8
57.5°	90.5
60°	56.0
62.5°	30.6
65°	14.7
67.5°	6.6
70°	4.0
72.5°	2.7
75°	2.7
77.5°	1.3
80°	1.3
82.5°	1.3
85°	1.3
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)