

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584177

Luminaire Tested: **HCC8W25D010MB-HM82555927-81WDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584177  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W25D010MB-HM82555927-81WDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2236.7 lumens  
Efficiency: N/A  
Efficacy: 83.5 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584177  
CATALOG NUMBER: HCC8W25D010MB-HM82555927-81WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P584177

CATALOG NUMBER: HCC8W25D010MB-HM82555927-81WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	96	93	104	99	95	92	96	92	90		93	90	88		90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81		86	83	79		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	71	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	61		68	64	60	59
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		63	59	55	54
8	74	63	57	52	73	63	56	52	62	56	52		60	55	51		59	55	51	50
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56	51	47	46
10	66	55	49	45	65	55	49	45	54	48	44		53	48	44		52	48	44	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	53668
5°	52223
10°	51825
15°	51053
20°	49505
25°	47658
30°	44519
35°	36842
40°	22240
45°	14984
50°	10794
55°	6156
60°	2714
65°	970
70°	361
75°	155
80°	0
85°	0



TEST NUMBER: P584177  
 CATALOG NUMBER: HCC8W25D010MB-HM82555927-81WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	160.3	7.2
10°-20°	449.4	20.1
20°-30°	641.1	28.7
30°-40°	583.8	26.1
40°-50°	275.4	12.3
50°-60°	108.3	4.8
60°-70°	17.2	0.8
70°-80°	1.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1250.8	55.9
0°-40°	1834.6	82.0
0°-60°	2218.3	99.2
0°-90°	2236.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2236.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1740	
5°	1687	160
15°	1599	449
25°	1401	641
35°	979	584
45°	344	275
55°	114	108
65°	13	17
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P584177  
CATALOG NUMBER: HCC8W25D010MB-HM82555927-81WDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1740.4
2.5°	1717.7
5°	1687.1
7.5°	1669.7
10°	1655.1
12.5°	1631.1
15°	1599.2
17.5°	1559.2
20°	1508.6
22.5°	1455.4
25°	1400.7
27.5°	1334.2
30°	1250.3
32.5°	1137.1
35°	978.7
37.5°	756.3
40°	552.5
42.5°	424.8
45°	343.6
47.5°	282.3
50°	225.0
52.5°	169.1
55°	114.5
57.5°	71.9
60°	44.0
62.5°	26.6
65°	13.3
67.5°	6.6
70°	4.0
72.5°	1.3
75°	1.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)