

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584169

Luminaire Tested: **HCC8W25D010MB-HM82555927-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584169
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W25D010MB-HM82555927-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1971.7 lumens
Efficiency: N/A
Efficacy: 73.6 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584169
CATALOG NUMBER: HCC8W25D010MB-HM82555927-81MDW

Luminous Intensity Polar Plot





TEST NUMBER: P584169
 CATALOG NUMBER: HCC8W25D010MB-HM82555927-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90		
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80		
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72		
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65		
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59		
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54		
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50		
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46		
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43		
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50420
5°	49047
10°	46151
15°	43695
20°	42033
25°	40410
30°	35888
35°	22854
40°	12756
45°	10684
50°	9647
55°	9091
60°	8295
65°	7479
70°	6600
75°	5862
80°	5203
85°	4706



TEST NUMBER: P584169
 CATALOG NUMBER: HCC8W25D010MB-HM82555927-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.7	7.5
10°-20°	386.0	19.6
20°-30°	538.5	27.3
30°-40°	387.5	19.7
40°-50°	192.1	9.7
50°-60°	150.3	7.6
60°-70°	101.7	5.2
70°-80°	52.8	2.7
80°-90°	15.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1072.3	54.4
0°-40°	1459.7	74.0
0°-60°	1802.1	91.4
0°-90°	1971.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1971.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1635	
5°	1584	148
15°	1369	386
25°	1188	539
35°	607	387
45°	245	192
55°	169	150
65°	102	102
75°	49	53
85°	13	15
90°	0	



TEST NUMBER: P584169
CATALOG NUMBER: HCC8W25D010MB-HM82555927-81MDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1635.1
2.5°	1620.4
5°	1584.5
7.5°	1533.8
10°	1473.9
12.5°	1418.1
15°	1368.7
17.5°	1322.2
20°	1280.9
22.5°	1239.6
25°	1187.7
27.5°	1113.1
30°	1007.9
32.5°	842.8
35°	607.1
37.5°	414.1
40°	316.9
42.5°	273.0
45°	245.0
47.5°	221.1
50°	201.1
52.5°	183.7
55°	169.1
57.5°	151.8
60°	134.5
62.5°	117.2
65°	102.5
67.5°	87.8
70°	73.2
72.5°	61.2
75°	49.2
77.5°	38.6
80°	29.3
82.5°	21.3
85°	13.3
87.5°	6.6
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)