

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584207

Luminaire Tested: **HCC8S25D010BZ-HM82555935-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584207
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010BZ-HM82555935-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2370.3 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584207
CATALOG NUMBER: HCC8S25D010BZ-HM82555935-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P584207
 CATALOG NUMBER: HCC8S25D010BZ-HM82555935-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	108	105	102	109	106	103	100	101	99	97		98	96	94		94	93	91	89
2	104	98	92	88	102	96	91	87	92	88	85		89	86	83		86	84	81	79
3	97	89	83	77	95	87	82	77	85	80	76		82	78	74		80	76	73	71
4	91	81	74	69	89	80	74	69	78	72	68		76	71	67		74	70	66	64
5	85	75	68	62	83	74	67	62	72	66	61		70	65	61		68	64	60	58
6	80	69	62	57	78	68	61	56	67	61	56		65	60	56		64	59	55	53
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		60	55	51	49
8	71	60	53	48	70	59	52	48	58	52	47		57	51	47		56	51	47	45
9	67	56	49	44	66	55	49	44	54	48	44		53	48	44		52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41		50	45	41		49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55638
5°	54916
10°	52902
15°	50836
20°	49426
25°	47940
30°	43016
35°	28199
40°	15590
45°	13000
50°	11854
55°	11311
60°	10521
65°	9544
70°	8628
75°	7792
80°	7068
85°	6793



TEST NUMBER: P584207
 CATALOG NUMBER: HCC8S25D010BZ-HM82555935-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.7	7.0
10°-20°	449.2	19.0
20°-30°	639.3	27.0
30°-40°	473.2	20.0
40°-50°	234.4	9.9
50°-60°	187.1	7.9
60°-70°	129.9	5.5
70°-80°	70.0	3.0
80°-90°	20.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1255.3	53.0
0°-40°	1728.4	72.9
0°-60°	2149.8	90.7
0°-90°	2370.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2370.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1804	
5°	1774	167
15°	1592	449
25°	1409	639
35°	749	473
45°	298	234
55°	210	187
65°	131	130
75°	65	70
85°	19	21
90°	0	



TEST NUMBER: P584207

CATALOG NUMBER: HCC8S25D010BZ-HM82555935-81PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1804.3
2.5°	1796.3
5°	1774.1
7.5°	1739.0
10°	1689.5
12.5°	1638.5
15°	1592.4
17.5°	1547.6
20°	1506.2
22.5°	1464.8
25°	1409.0
27.5°	1327.8
30°	1208.1
32.5°	1024.8
35°	749.1
37.5°	511.7
40°	387.3
42.5°	331.5
45°	298.1
47.5°	270.9
50°	247.1
52.5°	226.3
55°	210.4
57.5°	191.3
60°	170.6
62.5°	149.8
65°	130.8
67.5°	111.6
70°	95.7
72.5°	79.7
75°	65.4
77.5°	52.6
80°	39.8
82.5°	28.7
85°	19.2
87.5°	7.9
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)