

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584213

Luminaire Tested: **HCC8S25D010MB-HM82555935-81WDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584213  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S25D010MB-HM82555935-81WDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2448.3 lumens  
Efficiency: N/A  
Efficacy: 91.4 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584213  
CATALOG NUMBER: HCC8S25D010MB-HM82555935-81WDW

### Luminous Intensity Polar Plot





TEST NUMBER: P584213  
 CATALOG NUMBER: HCC8S25D010MB-HM82555935-81WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	48946
5°	48889
10°	48405
15°	47825
20°	47385
25°	46851
30°	44206
35°	35999
40°	19885
45°	13275
50°	11777
55°	11048
60°	10910
65°	10813
70°	9773
75°	8733
80°	7636
85°	6793



TEST NUMBER: P584213  
 CATALOG NUMBER: HCC8S25D010MB-HM82555935-81WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	149.7	6.1
10°-20°	423.0	17.3
20°-30°	628.5	25.7
30°-40°	566.0	23.1
40°-50°	250.9	10.2
50°-60°	185.8	7.6
60°-70°	144.5	5.9
70°-80°	78.3	3.2
80°-90°	21.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1201.2	49.1
0°-40°	1767.3	72.2
0°-60°	2204.0	90.0
0°-90°	2448.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2448.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1587	
5°	1579	150
15°	1498	423
25°	1377	629
35°	956	566
45°	304	251
55°	206	186
65°	148	144
75°	73	78
85°	19	21
90°	0	



TEST NUMBER: P584213  
CATALOG NUMBER: HCC8S25D010MB-HM82555935-81WDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1587.3
2.5°	1584.2
5°	1579.4
7.5°	1566.7
10°	1545.9
12.5°	1522.1
15°	1498.1
17.5°	1474.2
20°	1444.0
22.5°	1413.7
25°	1377.0
27.5°	1321.2
30°	1241.5
32.5°	1126.8
35°	956.3
37.5°	714.0
40°	494.0
42.5°	365.0
45°	304.4
47.5°	269.3
50°	245.5
52.5°	223.1
55°	205.5
57.5°	191.2
60°	176.9
62.5°	164.1
65°	148.2
67.5°	129.0
70°	108.4
72.5°	90.8
75°	73.3
77.5°	57.4
80°	43.0
82.5°	30.3
85°	19.2
87.5°	7.9
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)