

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593643

Luminaire Tested: **HCC8S25D010MW-HM82555950-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593643
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S25D010MW-HM82555950-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2609.4 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593643
CATALOG NUMBER: HCC8S25D010MW-HM82555950-81MDW

Luminous Intensity Polar Plot





TEST NUMBER: P593643

CATALOG NUMBER: HCC8S25D010MW-HM82555950-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92		90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82		80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74		72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67		65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61		59
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56		54
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52		50
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48		46
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45		43
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42		40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66724
5°	64908
10°	61077
15°	57827
20°	55625
25°	53476
30°	47496
35°	30247
40°	16878
45°	14138
50°	12766
55°	12026
60°	10972
65°	9901
70°	8736
75°	7768
80°	6872
85°	6262



TEST NUMBER: P593643
 CATALOG NUMBER: HCC8S25D010MW-HM82555950-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.5	7.5
10°-20°	510.9	19.6
20°-30°	712.7	27.3
30°-40°	512.8	19.7
40°-50°	254.1	9.7
50°-60°	198.8	7.6
60°-70°	134.6	5.2
70°-80°	69.9	2.7
80°-90°	20.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1419.0	54.4
0°-40°	1931.8	74.0
0°-60°	2384.7	91.4
0°-90°	2609.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2609.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2164	
5°	2097	195
15°	1811	511
25°	1572	713
35°	804	513
45°	324	254
55°	224	199
65°	136	135
75°	65	70
85°	18	20
90°	0	



TEST NUMBER: P593643
CATALOG NUMBER: HCC8S25D010MW-HM82555950-81MDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2163.8
2.5°	2144.4
5°	2096.9
7.5°	2029.9
10°	1950.6
12.5°	1876.6
15°	1811.4
17.5°	1749.8
20°	1695.1
22.5°	1640.5
25°	1571.7
27.5°	1473.1
30°	1333.9
32.5°	1115.4
35°	803.5
37.5°	547.9
40°	419.3
42.5°	361.2
45°	324.2
47.5°	292.5
50°	266.1
52.5°	243.2
55°	223.7
57.5°	200.8
60°	177.9
62.5°	155.0
65°	135.7
67.5°	116.3
70°	96.9
72.5°	81.1
75°	65.2
77.5°	51.1
80°	38.7
82.5°	28.1
85°	17.7
87.5°	8.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)