

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593645

Luminaire Tested: **HCC8W25D010SL-HM82555950-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593645
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W25D010SL-HM82555950-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2620.0 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593645
CATALOG NUMBER: HCC8W25D010SL-HM82555950-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P593645
 CATALOG NUMBER: HCC8W25D010SL-HM82555950-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89				
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79				
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71				
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64				
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58				
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53				
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49				
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45				
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42				
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61500
5°	60698
10°	58478
15°	56186
20°	54634
25°	52993
30°	47553
35°	31173
40°	17233
45°	14369
50°	13101
55°	12500
60°	11625
65°	10543
70°	9530
75°	8602
80°	7831
85°	7501



TEST NUMBER: P593645
 CATALOG NUMBER: HCC8W25D010SL-HM82555950-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.2	7.0
10°-20°	496.6	19.0
20°-30°	706.7	27.0
30°-40°	523.1	20.0
40°-50°	259.1	9.9
50°-60°	206.7	7.9
60°-70°	143.6	5.5
70°-80°	77.3	3.0
80°-90°	22.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1387.5	53.0
0°-40°	1910.6	72.9
0°-60°	2376.4	90.7
0°-90°	2620.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2620.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1994	
5°	1961	184
15°	1760	497
25°	1558	707
35°	828	523
45°	330	259
55°	232	207
65°	144	144
75°	72	77
85°	21	23
90°	0	



TEST NUMBER: P593645
CATALOG NUMBER: HCC8W25D010SL-HM82555950-81PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1994.4
2.5°	1985.6
5°	1960.9
7.5°	1922.1
10°	1867.6
12.5°	1811.2
15°	1760.0
17.5°	1710.7
20°	1664.9
22.5°	1619.1
25°	1557.5
27.5°	1467.6
30°	1335.5
32.5°	1132.9
35°	828.1
37.5°	565.6
40°	428.1
42.5°	366.5
45°	329.5
47.5°	299.5
50°	273.1
52.5°	250.2
55°	232.5
57.5°	211.4
60°	188.5
62.5°	165.6
65°	144.5
67.5°	123.4
70°	105.7
72.5°	88.1
75°	72.2
77.5°	58.1
80°	44.1
82.5°	31.7
85°	21.2
87.5°	8.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)