

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584261

Luminaire Tested: **HCC8W30D010MB-HM82555830-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584261
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W30D010MB-HM82555830-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3250.1 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584261
CATALOG NUMBER: HCC8W30D010MB-HM82555830-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P584261

CATALOG NUMBER: HCC8W30D010MB-HM82555830-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60896
5°	60388
10°	59593
15°	60273
20°	65089
25°	71175
30°	70316
35°	58330
40°	34333
45°	22433
50°	17385
55°	11553
60°	5625
65°	1744
70°	586
75°	524
80°	373
85°	743



TEST NUMBER: P584261
 CATALOG NUMBER: HCC8W30D010MB-HM82555830-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.8	5.7
10°-20°	542.4	16.7
20°-30°	948.3	29.2
30°-40°	922.5	28.4
40°-50°	419.6	12.9
50°-60°	194.5	6.0
60°-70°	32.6	1.0
70°-80°	4.0	0.1
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1675.5	51.6
0°-40°	2598.0	79.9
0°-60°	3212.1	98.8
0°-90°	3250.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3250.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1975	
5°	1951	185
15°	1888	542
25°	2092	948
35°	1550	923
45°	514	420
55°	215	195
65°	24	33
75°	4	4
85°	2	1
90°	0	



TEST NUMBER: P584261
CATALOG NUMBER: HCC8W30D010MB-HM82555830-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1974.8
2.5°	1970.4
5°	1950.9
7.5°	1929.3
10°	1903.2
12.5°	1883.6
15°	1888.0
17.5°	1922.7
20°	1983.5
22.5°	2052.9
25°	2091.9
27.5°	2070.3
30°	1974.8
32.5°	1807.8
35°	1549.5
37.5°	1193.5
40°	852.9
42.5°	635.9
45°	514.4
47.5°	434.0
50°	362.4
52.5°	288.6
55°	214.9
57.5°	147.6
60°	91.2
62.5°	49.9
65°	23.9
67.5°	10.8
70°	6.5
72.5°	4.4
75°	4.4
77.5°	2.1
80°	2.1
82.5°	2.1
85°	2.1
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)