

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584257

Luminaire Tested: **HCC8S30D010MW-HM82555830-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584257
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S30D010MW-HM82555830-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2905.1 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584257
CATALOG NUMBER: HCC8S30D010MW-HM82555830-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P584257
 CATALOG NUMBER: HCC8S30D010MW-HM82555830-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90				
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81				
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73				
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67				
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61				
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56				
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52				
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48				
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45				
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72413
5°	72219
10°	71016
15°	69978
20°	68299
25°	64833
30°	53474
35°	27533
40°	18432
45°	15804
50°	13639
55°	11903
60°	10577
65°	9500
70°	8610
75°	7768
80°	6943
85°	6899



TEST NUMBER: P584257
 CATALOG NUMBER: HCC8S30D010MW-HM82555830-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.6	7.6
10°-20°	616.7	21.2
20°-30°	854.5	29.4
30°-40°	513.2	17.7
40°-50°	281.0	9.7
50°-60°	199.6	6.9
60°-70°	129.6	4.5
70°-80°	69.3	2.4
80°-90°	20.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1691.8	58.2
0°-40°	2205.0	75.9
0°-60°	2685.6	92.4
0°-90°	2905.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2905.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2348	
5°	2333	221
15°	2192	617
25°	1906	854
35°	731	513
45°	362	281
55°	221	200
65°	130	130
75°	65	69
85°	20	21
90°	0	



TEST NUMBER: P584257
CATALOG NUMBER: HCC8S30D010MW-HM82555830-81NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2348.3
2.5°	2344.0
5°	2333.1
7.5°	2307.0
10°	2268.0
12.5°	2231.0
15°	2192.0
17.5°	2142.1
20°	2081.3
22.5°	2007.5
25°	1905.5
27.5°	1745.0
30°	1501.8
32.5°	1100.3
35°	731.4
37.5°	540.4
40°	457.9
42.5°	405.8
45°	362.4
47.5°	321.3
50°	284.3
52.5°	249.6
55°	221.4
57.5°	195.4
60°	171.5
62.5°	149.7
65°	130.2
67.5°	110.7
70°	95.5
72.5°	78.1
75°	65.2
77.5°	52.1
80°	39.1
82.5°	28.2
85°	19.5
87.5°	8.7
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)