

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584290

Luminaire Tested: **HCC8S30D010BZ-HM82555840-81NDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584290
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S30D010BZ-HM82555840-81NDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3372.6 lumens
Efficiency: N/A
Efficacy: 120.4 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584290
CATALOG NUMBER: HCC8S30D010BZ-HM82555840-81NDH

Luminous Intensity Polar Plot





TEST NUMBER: P584290

CATALOG NUMBER: HCC8S30D010BZ-HM82555840-81NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75
6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72
7	88	80	74	70	87	79	74	70	78	73	70	77	73	70	76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	268362
5°	227355
10°	164958
15°	123878
20°	97744
25°	78841
30°	58423
35°	23667
40°	9983
45°	5351
50°	2403
55°	1215
60°	771
65°	547
70°	451
75°	298
80°	444
85°	885



TEST NUMBER: P584290
 CATALOG NUMBER: HCC8S30D010BZ-HM82555840-81NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	630.6	18.7
10°-20°	1089.9	32.3
20°-30°	1053.7	31.2
30°-40°	462.8	13.7
40°-50°	100.0	3.0
50°-60°	22.5	0.7
60°-70°	7.7	0.2
70°-80°	3.0	0.1
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2774.3	82.3
0°-40°	3237.0	96.0
0°-60°	3359.5	99.6
0°-90°	3372.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3372.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8703	
5°	7345	631
15°	3880	1090
25°	2317	1054
35°	629	463
45°	123	100
55°	23	22
65°	8	8
75°	2	3
85°	2	2
90°	0	



TEST NUMBER: P584290
CATALOG NUMBER: HCC8S30D010BZ-HM82555840-81NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	8702.8
1°	8637.6
2°	8459.7
3°	8139.1
4°	7755.8
5°	7344.9
6°	6896.6
7°	6445.7
8°	6022.3
9°	5629.0
10°	5268.2
11°	4927.6
12°	4621.9
13°	4343.9
14°	4098.4
15°	3880.4
17.5°	3392.0
20°	2978.6
22.5°	2615.3
25°	2317.2
27.5°	2014.2
30°	1640.8
32.5°	1114.8
35°	628.7
37.5°	370.7
40°	248.0
42.5°	175.4
45°	122.7
47.5°	80.1
50°	50.1
52.5°	30.1
55°	22.6
57.5°	17.5
60°	12.5
62.5°	10.0
65°	7.5
67.5°	5.0
70°	5.0
72.5°	2.5
75°	2.5
77.5°	2.5
80°	2.5
82.5°	2.5

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P584290
CATALOG NUMBER: HCC8S30D010BZ-HM82555840-81NDH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



85°	2.5
87.5°	2.5

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)