

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584291

Luminaire Tested: **HCC8W30D010MW-HM82555840-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584291
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W30D010MW-HM82555840-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3335.3 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584291
CATALOG NUMBER: HCC8W30D010MW-HM82555840-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P584291

CATALOG NUMBER: HCC8W30D010MW-HM82555840-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	83132
5°	82914
10°	81530
15°	80340
20°	78412
25°	74431
30°	61397
35°	31610
40°	21166
45°	18150
50°	15658
55°	13666
60°	12143
65°	10908
70°	9881
75°	8912
80°	7956
85°	7961



TEST NUMBER: P584291
 CATALOG NUMBER: HCC8W30D010MW-HM82555840-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	253.3	7.6
10°-20°	708.0	21.2
20°-30°	981.0	29.4
30°-40°	589.3	17.7
40°-50°	322.6	9.7
50°-60°	229.2	6.9
60°-70°	148.8	4.5
70°-80°	79.5	2.4
80°-90°	23.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1942.3	58.2
0°-40°	2531.6	75.9
0°-60°	3083.3	92.4
0°-90°	3335.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3335.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2696	
5°	2679	253
15°	2517	708
25°	2188	981
35°	840	589
45°	416	323
55°	254	229
65°	150	149
75°	75	79
85°	22	24
90°	0	



TEST NUMBER: P584291
CATALOG NUMBER: HCC8W30D010MW-HM82555840-81NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2695.9
2.5°	2690.9
5°	2678.6
7.5°	2648.6
10°	2603.8
12.5°	2561.5
15°	2516.6
17.5°	2459.3
20°	2389.5
22.5°	2304.8
25°	2187.6
27.5°	2003.3
30°	1724.3
32.5°	1263.3
35°	839.7
37.5°	620.4
40°	525.8
42.5°	466.0
45°	416.2
47.5°	368.7
50°	326.4
52.5°	286.5
55°	254.2
57.5°	224.2
60°	196.9
62.5°	171.9
65°	149.5
67.5°	127.1
70°	109.6
72.5°	89.7
75°	74.8
77.5°	59.8
80°	44.8
82.5°	32.3
85°	22.5
87.5°	10.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)