

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593652

Luminaire Tested: **HCC8W30D010MB-HM82555850-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593652
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W30D010MB-HM82555850-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3731.3 lumens
Efficiency: N/A
Efficacy: 133.3 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593652
CATALOG NUMBER: HCC8W30D010MB-HM82555850-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P593652
 CATALOG NUMBER: HCC8W30D010MB-HM82555850-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69912
5°	69328
10°	68414
15°	69195
20°	74727
25°	81716
30°	80728
35°	66965
40°	39413
45°	25751
50°	19957
55°	13258
60°	6451
65°	1992
70°	676
75°	596
80°	444
85°	885



TEST NUMBER: P593652
 CATALOG NUMBER: HCC8W30D010MB-HM82555850-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	212.1	5.7
10°-20°	622.7	16.7
20°-30°	1088.7	29.2
30°-40°	1059.1	28.4
40°-50°	481.6	12.9
50°-60°	223.3	6.0
60°-70°	37.4	1.0
70°-80°	4.6	0.1
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1923.6	51.6
0°-40°	2982.7	79.9
0°-60°	3687.6	98.8
0°-90°	3731.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3731.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2267	
5°	2240	212
15°	2168	623
25°	2402	1089
35°	1779	1059
45°	590	482
55°	247	223
65°	27	37
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P593652
CATALOG NUMBER: HCC8W30D010MB-HM82555850-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2267.2
2.5°	2262.2
5°	2239.7
7.5°	2214.9
10°	2184.9
12.5°	2162.6
15°	2167.5
17.5°	2207.4
20°	2277.2
22.5°	2356.8
25°	2401.7
27.5°	2376.8
30°	2267.2
32.5°	2075.4
35°	1778.9
37.5°	1370.3
40°	979.1
42.5°	729.9
45°	590.5
47.5°	498.3
50°	416.0
52.5°	331.4
55°	246.6
57.5°	169.4
60°	104.6
62.5°	57.3
65°	27.3
67.5°	12.5
70°	7.5
72.5°	5.0
75°	5.0
77.5°	2.5
80°	2.5
82.5°	2.5
85°	2.5
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)