

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584316

Luminaire Tested: **HCC8S30D010MW-HM82555927-81WDWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584316
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S30D010MW-HM82555927-81WDWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2950.5 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584316
CATALOG NUMBER: HCC8S30D010MW-HM82555927-81WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P584316
 CATALOG NUMBER: HCC8S30D010MW-HM82555927-81WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92		90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83		81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74		73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67		65
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61		59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56		54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51		49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47		45
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43		41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40		38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51817
5°	51461
10°	51327
15°	52675
20°	57023
25°	61135
30°	59769
35°	49773
40°	30573
45°	21172
50°	16157
55°	10591
60°	6630
65°	4969
70°	5004
75°	5766
80°	6357
85°	5732



TEST NUMBER: P584316
 CATALOG NUMBER: HCC8S30D010MW-HM82555927-81WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.0	5.4
10°-20°	473.6	16.1
20°-30°	815.4	27.6
30°-40°	790.0	26.8
40°-50°	389.1	13.2
50°-60°	183.6	6.2
60°-70°	72.4	2.5
70°-80°	49.9	1.7
80°-90°	18.5	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1447.0	49.0
0°-40°	2237.0	75.8
0°-60°	2809.6	95.2
0°-90°	2950.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2950.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1680	
5°	1662	158
15°	1650	474
25°	1797	815
35°	1322	790
45°	486	389
55°	197	184
65°	68	72
75°	48	50
85°	16	19
90°	0	



TEST NUMBER: P584316
CATALOG NUMBER: HCC8S30D010MW-HM82555927-81WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1680.4
2.5°	1675.1
5°	1662.5
7.5°	1650.0
10°	1639.2
12.5°	1637.4
15°	1650.0
17.5°	1687.5
20°	1737.7
22.5°	1782.5
25°	1796.8
27.5°	1764.6
30°	1678.6
32.5°	1537.1
35°	1322.2
37.5°	1026.5
40°	759.5
42.5°	589.4
45°	485.5
47.5°	408.4
50°	336.8
52.5°	265.1
55°	197.0
57.5°	143.3
60°	107.5
62.5°	84.2
65°	68.1
67.5°	59.1
70°	55.5
72.5°	52.0
75°	48.4
77.5°	43.0
80°	35.8
82.5°	26.9
85°	16.2
87.5°	7.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)