

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584364

Luminaire Tested: **HCC8S30D010SL-HM82555940-81WDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584364  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S30D010SL-HM82555940-81WDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3982.8 lumens  
Efficiency: N/A  
Efficacy: 142.2 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584364  
CATALOG NUMBER: HCC8S30D010SL-HM82555940-81WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P584364

CATALOG NUMBER: HCC8S30D010SL-HM82555940-81WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84		
3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77		
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70		
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64		
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59		
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54		
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50		
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46		
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	95556
5°	92986
10°	92280
15°	90904
20°	88152
25°	84863
30°	79271
35°	65599
40°	39606
45°	26676
50°	19223
55°	10962
60°	4823
65°	1729
70°	640
75°	286
80°	0
85°	0



TEST NUMBER: P584364  
 CATALOG NUMBER: HCC8S30D010SL-HM82555940-81WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	285.4	7.2
10°-20°	800.2	20.1
20°-30°	1141.5	28.7
30°-40°	1039.5	26.1
40°-50°	490.4	12.3
50°-60°	192.9	4.8
60°-70°	30.7	0.8
70°-80°	2.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2227.2	55.9
0°-40°	3266.7	82.0
0°-60°	3949.9	99.2
0°-90°	3982.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3982.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3099	
5°	3004	285
15°	2848	800
25°	2494	1142
35°	1743	1039
45°	612	490
55°	204	193
65°	24	31
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P584364  
CATALOG NUMBER: HCC8S30D010SL-HM82555940-81WDC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3098.8
2.5°	3058.5
5°	3004.0
7.5°	2973.1
10°	2947.1
12.5°	2904.4
15°	2847.5
17.5°	2776.3
20°	2686.3
22.5°	2591.4
25°	2494.2
27.5°	2375.6
30°	2226.3
32.5°	2024.7
35°	1742.6
37.5°	1346.7
40°	983.9
42.5°	756.3
45°	611.7
47.5°	502.6
50°	400.7
52.5°	301.1
55°	203.9
57.5°	128.1
60°	78.2
62.5°	47.4
65°	23.7
67.5°	11.9
70°	7.1
72.5°	2.4
75°	2.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)