

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593679

Luminaire Tested: **HCC8S30D010MW-HM82555950-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593679
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S30D010MW-HM82555950-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3525.2 lumens
Efficiency: N/A
Efficacy: 125.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593679
CATALOG NUMBER: HCC8S30D010MW-HM82555950-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P593679

CATALOG NUMBER: HCC8S30D010MW-HM82555950-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89			89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79			79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64			64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49			49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45			45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82749
5°	81669
10°	78681
15°	75606
20°	73513
25°	71301
30°	63982
35°	41943
40°	23190
45°	19332
50°	17625
55°	16822
60°	15640
65°	14184
70°	12821
75°	11569
80°	10513
85°	10048



TEST NUMBER: P593679
 CATALOG NUMBER: HCC8S30D010MW-HM82555950-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	247.9	7.0
10°-20°	668.1	19.0
20°-30°	950.9	27.0
30°-40°	703.8	20.0
40°-50°	348.6	9.9
50°-60°	278.2	7.9
60°-70°	193.1	5.5
70°-80°	104.0	3.0
80°-90°	30.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1866.9	53.0
0°-40°	2570.7	72.9
0°-60°	3197.4	90.7
0°-90°	3525.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3525.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2684	
5°	2638	248
15°	2368	668
25°	2096	951
35°	1114	704
45°	443	349
55°	313	278
65°	194	193
75°	97	104
85°	28	31
90°	0	



TEST NUMBER: P593679

CATALOG NUMBER: HCC8S30D010MW-HM82555950-81PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2683.5
2.5°	2671.7
5°	2638.4
7.5°	2586.3
10°	2512.8
12.5°	2437.0
15°	2368.3
17.5°	2301.8
20°	2240.2
22.5°	2178.6
25°	2095.6
27.5°	1974.7
30°	1796.9
32.5°	1524.3
35°	1114.2
37.5°	761.0
40°	576.1
42.5°	493.1
45°	443.3
47.5°	403.0
50°	367.4
52.5°	336.6
55°	312.9
57.5°	284.4
60°	253.6
62.5°	222.8
65°	194.4
67.5°	166.0
70°	142.2
72.5°	118.5
75°	97.1
77.5°	78.2
80°	59.2
82.5°	42.7
85°	28.4
87.5°	11.9
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)