

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584372

Luminaire Tested: **HCC8W35D010MW-HM82555827-81MDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584372
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W35D010MW-HM82555827-81MDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3943.7 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584372
CATALOG NUMBER: HCC8W35D010MW-HM82555827-81MDH

Luminous Intensity Polar Plot





TEST NUMBER: P584372

CATALOG NUMBER: HCC8W35D010MW-HM82555827-81MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58			
9	76	67	61	57	75	66	61	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	180359
5°	164357
10°	140425
15°	122464
20°	109150
25°	96822
30°	79275
35°	45523
40°	20199
45°	11761
50°	6788
55°	3876
60°	2140
65°	1364
70°	965
75°	643
80°	462
85°	920



TEST NUMBER: P584372
 CATALOG NUMBER: HCC8W35D010MW-HM82555827-81MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	480.6	12.2
10°-20°	1078.3	27.3
20°-30°	1290.7	32.7
30°-40°	780.8	19.8
40°-50°	218.9	5.5
50°-60°	67.9	1.7
60°-70°	19.4	0.5
70°-80°	5.3	0.1
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2849.7	72.3
0°-40°	3630.5	92.1
0°-60°	3917.3	99.3
0°-90°	3943.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3943.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5849	
5°	5310	481
15°	3836	1078
25°	2846	1291
35°	1209	781
45°	270	219
55°	72	68
65°	19	19
75°	5	5
85°	3	2
90°	0	



TEST NUMBER: P584372
CATALOG NUMBER: HCC8W35D010MW-HM82555827-81MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5848.9
2.5°	5683.3
5°	5309.7
7.5°	4887.8
10°	4484.7
12.5°	4132.4
15°	3836.1
17.5°	3574.5
20°	3326.2
22.5°	3096.6
25°	2845.7
27.5°	2562.8
30°	2226.4
32.5°	1791.2
35°	1209.3
37.5°	752.8
40°	501.8
42.5°	360.4
45°	269.7
47.5°	197.6
50°	141.5
52.5°	98.7
55°	72.1
57.5°	48.0
60°	34.7
62.5°	24.1
65°	18.7
67.5°	13.3
70°	10.7
72.5°	5.4
75°	5.4
77.5°	2.6
80°	2.6
82.5°	2.6
85°	2.6
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)