

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584411

Luminaire Tested: **HCC8W35D010MB-HM82555835-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584411
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W35D010MB-HM82555835-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4109.9 lumens
Efficiency: N/A
Efficacy: 122.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584411
CATALOG NUMBER: HCC8W35D010MB-HM82555835-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P584411
 CATALOG NUMBER: HCC8W35D010MB-HM82555835-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89				
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79				
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71				
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64				
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58				
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53				
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49				
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45				
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42				
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	96474
5°	95215
10°	91732
15°	88139
20°	85707
25°	83124
30°	74592
35°	48900
40°	27035
45°	22537
50°	20552
55°	19612
60°	18237
65°	16541
70°	14948
75°	13499
80°	12271
85°	11746



TEST NUMBER: P584411
 CATALOG NUMBER: HCC8W35D010MB-HM82555835-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	289.0	7.0
10°-20°	778.9	19.0
20°-30°	1108.6	27.0
30°-40°	820.5	20.0
40°-50°	406.4	9.9
50°-60°	324.3	7.9
60°-70°	225.2	5.5
70°-80°	121.3	3.0
80°-90°	35.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2176.5	53.0
0°-40°	2997.0	72.9
0°-60°	3727.7	90.7
0°-90°	4109.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4109.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3129	
5°	3076	289
15°	2761	779
25°	2443	1109
35°	1299	820
45°	517	406
55°	365	324
65°	227	225
75°	113	121
85°	33	36
90°	0	



TEST NUMBER: P584411
CATALOG NUMBER: HCC8W35D010MB-HM82555835-81PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3128.6
2.5°	3114.7
5°	3076.0
7.5°	3015.2
10°	2929.6
12.5°	2841.1
15°	2760.9
17.5°	2683.5
20°	2611.8
22.5°	2539.9
25°	2443.1
27.5°	2302.2
30°	2094.9
32.5°	1777.1
35°	1299.0
37.5°	887.1
40°	671.6
42.5°	574.8
45°	516.8
47.5°	469.9
50°	428.4
52.5°	392.5
55°	364.8
57.5°	331.6
60°	295.7
62.5°	259.8
65°	226.7
67.5°	193.5
70°	165.8
72.5°	138.1
75°	113.3
77.5°	91.2
80°	69.1
82.5°	49.7
85°	33.2
87.5°	13.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)