

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584427

Luminaire Tested: **HCC8S35D010MB-HM82555840-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584427
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S35D010MB-HM82555840-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4008.2 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584427
CATALOG NUMBER: HCC8S35D010MB-HM82555840-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P584427
 CATALOG NUMBER: HCC8S35D010MB-HM82555840-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95	93	92	90
2	105	99	94	90	102	97	92	88	94	90	87		91	87	85		88	85	83	81
3	98	90	84	79	96	89	83	79	86	81	77		84	80	76		81	78	75	73
4	92	83	76	71	90	82	76	71	80	74	70		77	73	69		75	72	68	67
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66	61	58	56
7	77	66	59	54	76	66	59	54	64	58	54		63	58	54		62	57	53	52
8	73	62	55	50	71	61	55	50	60	54	50		59	54	50		58	53	49	48
9	69	58	51	47	68	57	51	47	56	51	46		55	50	46		55	50	46	45
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99907
5°	99638
10°	97982
15°	96551
20°	94232
25°	89449
30°	73781
35°	37987
40°	25432
45°	21805
50°	18815
55°	16419
60°	14592
65°	13112
70°	11883
75°	10699
80°	9572
85°	9553



TEST NUMBER: P584427
 CATALOG NUMBER: HCC8S35D010MB-HM82555840-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	304.4	7.6
10°-20°	850.9	21.2
20°-30°	1178.9	29.4
30°-40°	708.1	17.7
40°-50°	387.6	9.7
50°-60°	275.4	6.9
60°-70°	178.8	4.5
70°-80°	95.5	2.4
80°-90°	28.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2334.2	58.2
0°-40°	3042.3	75.9
0°-60°	3705.3	92.4
0°-90°	4008.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4008.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3240	
5°	3219	304
15°	3024	851
25°	2629	1179
35°	1009	708
45°	500	388
55°	305	275
65°	180	179
75°	90	96
85°	27	29
90°	0	



TEST NUMBER: P584427
CATALOG NUMBER: HCC8S35D010MB-HM82555840-81NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3239.9
2.5°	3233.9
5°	3218.9
7.5°	3183.1
10°	3129.2
12.5°	3078.3
15°	3024.4
17.5°	2955.5
20°	2871.6
22.5°	2769.8
25°	2629.0
27.5°	2407.5
30°	2072.1
32.5°	1518.1
35°	1009.1
37.5°	745.6
40°	631.8
42.5°	559.9
45°	500.0
47.5°	443.1
50°	392.2
52.5°	344.3
55°	305.4
57.5°	269.6
60°	236.6
62.5°	206.7
65°	179.7
67.5°	152.7
70°	131.8
72.5°	107.8
75°	89.8
77.5°	71.9
80°	53.9
82.5°	38.9
85°	27.0
87.5°	12.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)