

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584428

Luminaire Tested: **HCC8W35D010BZ-HM82555840-81PSMDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584428  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W35D010BZ-HM82555840-81PSMDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4451.3 lumens  
Efficiency: N/A  
Efficacy: 132.1 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584428  
CATALOG NUMBER: HCC8W35D010BZ-HM82555840-81PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P584428  
 CATALOG NUMBER: HCC8W35D010BZ-HM82555840-81PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	104483
5°	103124
10°	99350
15°	95459
20°	92821
25°	90028
30°	80788
35°	52958
40°	29277
45°	24408
50°	22259
55°	21241
60°	19748
65°	17913
70°	16193
75°	14619
80°	13301
85°	12702



TEST NUMBER: P584428  
 CATALOG NUMBER: HCC8W35D010BZ-HM82555840-81PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	313.0	7.0
10°-20°	843.6	19.0
20°-30°	1200.6	27.0
30°-40°	888.6	20.0
40°-50°	440.1	9.9
50°-60°	351.3	7.9
60°-70°	243.9	5.5
70°-80°	131.4	3.0
80°-90°	38.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2357.3	53.0
0°-40°	3245.9	72.9
0°-60°	4037.3	90.7
0°-90°	4451.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4451.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3388	
5°	3332	313
15°	2990	844
25°	2646	1201
35°	1407	889
45°	560	440
55°	395	351
65°	246	244
75°	123	131
85°	36	39
90°	0	



TEST NUMBER: P584428  
CATALOG NUMBER: HCC8W35D010BZ-HM82555840-81PSMDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3388.3
2.5°	3373.4
5°	3331.5
7.5°	3265.6
10°	3172.9
12.5°	3077.1
15°	2990.2
17.5°	2906.5
20°	2828.6
22.5°	2750.8
25°	2646.0
27.5°	2493.4
30°	2268.9
32.5°	1924.7
35°	1406.8
37.5°	960.8
40°	727.3
42.5°	622.6
45°	559.7
47.5°	508.9
50°	464.0
52.5°	425.1
55°	395.1
57.5°	359.2
60°	320.2
62.5°	281.4
65°	245.5
67.5°	209.5
70°	179.6
72.5°	149.6
75°	122.7
77.5°	98.8
80°	74.9
82.5°	53.9
85°	35.9
87.5°	15.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)