

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593690

Luminaire Tested: **HCC8S35D010BZ-HM82555850-81WDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593690  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S35D010BZ-HM82555850-81WDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4762.6 lumens  
Efficiency: N/A  
Efficacy: 141.3 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593690  
CATALOG NUMBER: HCC8S35D010BZ-HM82555850-81WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P593690

CATALOG NUMBER: HCC8S35D010BZ-HM82555850-81WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75		
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68		
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62		
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57		
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52		
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48		
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44		
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	109034
5°	106578
10°	103311
15°	101219
20°	100310
25°	98813
30°	93599
35°	77765
40°	45797
45°	30291
50°	23847
55°	17542
60°	12187
65°	7428
70°	3237
75°	1430
80°	1065
85°	0



TEST NUMBER: P593690  
 CATALOG NUMBER: HCC8S35D010BZ-HM82555850-81WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	324.2	6.8
10°-20°	896.4	18.8
20°-30°	1328.0	27.9
30°-40°	1227.2	25.8
40°-50°	565.8	11.9
50°-60°	297.6	6.2
60°-70°	105.2	2.2
70°-80°	16.5	0.3
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2548.6	53.5
0°-40°	3775.8	79.3
0°-60°	4639.3	97.4
0°-90°	4762.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4762.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3536	
5°	3443	324
15°	3171	896
25°	2904	1328
35°	2066	1227
45°	695	566
55°	326	298
65°	102	105
75°	12	17
85°	0	2
90°	0	



TEST NUMBER: P593690

CATALOG NUMBER: HCC8S35D010BZ-HM82555850-81WDH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3535.9
2.5°	3505.9
5°	3443.1
7.5°	3374.2
10°	3299.4
12.5°	3227.5
15°	3170.6
17.5°	3119.7
20°	3056.8
22.5°	2987.9
25°	2904.2
27.5°	2790.4
30°	2628.7
32.5°	2398.2
35°	2065.8
37.5°	1586.8
40°	1137.7
42.5°	853.3
45°	694.6
47.5°	589.8
50°	497.1
52.5°	407.2
55°	326.3
57.5°	257.5
60°	197.6
62.5°	149.8
65°	101.8
67.5°	59.9
70°	35.9
72.5°	21.0
75°	12.0
77.5°	9.0
80°	6.0
82.5°	3.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)