

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593687

Luminaire Tested: **HCC8S35D010MW-HM82555850-81WDWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593687
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S35D010MW-HM82555850-81WDWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4930.3 lumens
Efficiency: N/A
Efficacy: 146.3 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593687
CATALOG NUMBER: HCC8S35D010MW-HM82555850-81WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P593687
 CATALOG NUMBER: HCC8S35D010MW-HM82555850-81WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92		90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83		81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74		73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67		65
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61		59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56		54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51		49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47		45
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43		41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40		38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86585
5°	85991
10°	85767
15°	88018
20°	95286
25°	102157
30°	99873
35°	83164
40°	51094
45°	35380
50°	26999
55°	17704
60°	11076
65°	8303
70°	8367
75°	9639
80°	10637
85°	9553



TEST NUMBER: P593687
 CATALOG NUMBER: HCC8S35D010MW-HM82555850-81WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	264.0	5.4
10°-20°	791.5	16.1
20°-30°	1362.5	27.6
30°-40°	1320.0	26.8
40°-50°	650.2	13.2
50°-60°	306.8	6.2
60°-70°	120.9	2.5
70°-80°	83.5	1.7
80°-90°	31.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2417.9	49.0
0°-40°	3737.9	75.8
0°-60°	4695.0	95.2
0°-90°	4930.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4930.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2808	
5°	2778	264
15°	2757	791
25°	3002	1362
35°	2209	1320
45°	811	650
55°	329	307
65°	114	121
75°	81	83
85°	27	31
90°	0	



TEST NUMBER: P593687
CATALOG NUMBER: HCC8S35D010MW-HM82555850-81WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2807.9
2.5°	2798.9
5°	2778.0
7.5°	2757.1
10°	2739.1
12.5°	2736.1
15°	2757.1
17.5°	2819.9
20°	2903.7
22.5°	2978.6
25°	3002.5
27.5°	2948.6
30°	2804.9
32.5°	2568.4
35°	2209.2
37.5°	1715.3
40°	1269.3
42.5°	984.9
45°	811.3
47.5°	682.5
50°	562.8
52.5°	443.0
55°	329.3
57.5°	239.5
60°	179.6
62.5°	140.6
65°	113.8
67.5°	98.8
70°	92.8
72.5°	86.9
75°	80.9
77.5°	71.9
80°	59.9
82.5°	44.9
85°	27.0
87.5°	12.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)