

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584450

Luminaire Tested: **HCC8S35D010MB-HM82555927-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584450
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S35D010MB-HM82555927-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3425.3 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584450
CATALOG NUMBER: HCC8S35D010MB-HM82555927-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P584450

CATALOG NUMBER: HCC8S35D010MB-HM82555927-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68			
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78417
5°	76652
10°	74300
15°	72797
20°	72141
25°	71066
30°	67318
35°	55932
40°	32936
45°	21787
50°	17150
55°	12618
60°	8764
65°	5341
70°	2335
75°	1025
80°	764
85°	0



TEST NUMBER: P584450
 CATALOG NUMBER: HCC8S35D010MB-HM82555927-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.2	6.8
10°-20°	644.7	18.8
20°-30°	955.1	27.9
30°-40°	882.6	25.8
40°-50°	407.0	11.9
50°-60°	214.0	6.2
60°-70°	75.6	2.2
70°-80°	11.9	0.3
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1833.0	53.5
0°-40°	2715.6	79.3
0°-60°	3336.6	97.4
0°-90°	3425.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3425.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2543	
5°	2476	233
15°	2280	645
25°	2089	955
35°	1486	883
45°	500	407
55°	235	214
65°	73	76
75°	9	12
85°	0	1
90°	0	



TEST NUMBER: P584450
CATALOG NUMBER: HCC8S35D010MB-HM82555927-81WDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2543.0
2.5°	2521.4
5°	2476.3
7.5°	2426.8
10°	2372.9
12.5°	2321.2
15°	2280.3
17.5°	2243.7
20°	2198.4
22.5°	2149.0
25°	2088.7
27.5°	2006.9
30°	1890.6
32.5°	1724.8
35°	1485.8
37.5°	1141.2
40°	818.2
42.5°	613.7
45°	499.6
47.5°	424.2
50°	357.5
52.5°	292.8
55°	234.7
57.5°	185.2
60°	142.1
62.5°	107.7
65°	73.2
67.5°	43.0
70°	25.9
72.5°	15.1
75°	8.6
77.5°	6.5
80°	4.3
82.5°	2.2
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)