

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584479

Luminaire Tested: **HCC8W35D010MB-HM82555935-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584479
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W35D010MB-HM82555935-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3832.8 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584479
CATALOG NUMBER: HCC8W35D010MB-HM82555935-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P584479
 CATALOG NUMBER: HCC8W35D010MB-HM82555935-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71		
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64		
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58		
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53		
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49		
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45		
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42		
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	89965
5°	88792
10°	85541
15°	82195
20°	79922
25°	77521
30°	69561
35°	45598
40°	25211
45°	21020
50°	19165
55°	18290
60°	17009
65°	15417
70°	13948
75°	12593
80°	11454
85°	10933



TEST NUMBER: P584479
 CATALOG NUMBER: HCC8W35D010MB-HM82555935-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	269.5	7.0
10°-20°	726.4	19.0
20°-30°	1033.8	27.0
30°-40°	765.1	20.0
40°-50°	379.0	9.9
50°-60°	302.5	7.9
60°-70°	209.9	5.5
70°-80°	113.2	3.0
80°-90°	33.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2029.7	53.0
0°-40°	2794.9	72.9
0°-60°	3476.3	90.7
0°-90°	3832.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3832.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2918	
5°	2868	270
15°	2575	726
25°	2278	1034
35°	1211	765
45°	482	379
55°	340	302
65°	211	210
75°	106	113
85°	31	33
90°	0	



TEST NUMBER: P584479
CATALOG NUMBER: HCC8W35D010MB-HM82555935-81PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2917.5
2.5°	2904.7
5°	2868.5
7.5°	2811.8
10°	2731.9
12.5°	2649.5
15°	2574.7
17.5°	2502.6
20°	2435.5
22.5°	2368.6
25°	2278.4
27.5°	2146.9
30°	1953.6
32.5°	1657.2
35°	1211.3
37.5°	827.3
40°	626.3
42.5°	536.1
45°	482.0
47.5°	438.1
50°	399.5
52.5°	366.0
55°	340.2
57.5°	309.3
60°	275.8
62.5°	242.2
65°	211.3
67.5°	180.4
70°	154.7
72.5°	128.9
75°	105.7
77.5°	85.1
80°	64.5
82.5°	46.4
85°	30.9
87.5°	12.9
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)