

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584496

Luminaire Tested: **HCC8W35D010MB-HM82555940-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584496
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W35D010MB-HM82555940-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4236.6 lumens
Efficiency: N/A
Efficacy: 125.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584496
CATALOG NUMBER: HCC8W35D010MB-HM82555940-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P584496

CATALOG NUMBER: HCC8W35D010MB-HM82555940-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89			89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79			79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64			64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49			49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45			45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99444
5°	98146
10°	94556
15°	90856
20°	88342
25°	85686
30°	76889
35°	50406
40°	27868
45°	23235
50°	21185
55°	20220
60°	18798
65°	17045
70°	15417
75°	13916
80°	12661
85°	12065



TEST NUMBER: P584496
 CATALOG NUMBER: HCC8W35D010MB-HM82555940-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	297.9	7.0
10°-20°	802.9	19.0
20°-30°	1142.7	27.0
30°-40°	845.8	20.0
40°-50°	418.9	9.9
50°-60°	334.4	7.9
60°-70°	232.1	5.5
70°-80°	125.1	3.0
80°-90°	36.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2243.6	53.0
0°-40°	3089.3	72.9
0°-60°	3842.6	90.7
0°-90°	4236.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4236.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3225	
5°	3171	298
15°	2846	803
25°	2518	1143
35°	1339	846
45°	533	419
55°	376	334
65°	234	232
75°	117	125
85°	34	37
90°	0	



TEST NUMBER: P584496
CATALOG NUMBER: HCC8W35D010MB-HM82555940-81PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3224.9
2.5°	3210.6
5°	3170.7
7.5°	3108.1
10°	3019.8
12.5°	2928.6
15°	2846.0
17.5°	2766.2
20°	2692.1
22.5°	2618.1
25°	2518.4
27.5°	2373.1
30°	2159.4
32.5°	1831.9
35°	1339.0
37.5°	914.4
40°	692.3
42.5°	592.5
45°	532.8
47.5°	484.4
50°	441.6
52.5°	404.6
55°	376.1
57.5°	341.9
60°	304.8
62.5°	267.8
65°	233.6
67.5°	199.5
70°	171.0
72.5°	142.4
75°	116.8
77.5°	94.0
80°	71.3
82.5°	51.3
85°	34.1
87.5°	14.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)