

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584516

Luminaire Tested: **HCC8S40D010MW-HM82555827-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584516
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S40D010MW-HM82555827-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4634.3 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584516
CATALOG NUMBER: HCC8S40D010MW-HM82555827-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P584516

CATALOG NUMBER: HCC8S40D010MW-HM82555827-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86829
5°	86105
10°	84971
15°	85940
20°	92808
25°	101494
30°	100261
35°	83171
40°	48953
45°	31983
50°	24788
55°	16467
60°	8011
65°	2481
70°	838
75°	739
80°	550
85°	1097



TEST NUMBER: P584516
 CATALOG NUMBER: HCC8S40D010MW-HM82555827-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	263.4	5.7
10°-20°	773.4	16.7
20°-30°	1352.2	29.2
30°-40°	1315.4	28.4
40°-50°	598.2	12.9
50°-60°	277.3	6.0
60°-70°	46.5	1.0
70°-80°	5.7	0.1
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2389.1	51.6
0°-40°	3704.4	79.9
0°-60°	4580.0	98.8
0°-90°	4634.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4634.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2816	
5°	2782	263
15°	2692	773
25°	2983	1352
35°	2209	1315
45°	733	598
55°	306	277
65°	34	46
75°	6	6
85°	3	2
90°	0	



TEST NUMBER: P584516
CATALOG NUMBER: HCC8S40D010MW-HM82555827-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2815.8
2.5°	2809.6
5°	2781.7
7.5°	2750.8
10°	2713.7
12.5°	2685.8
15°	2692.0
17.5°	2741.5
20°	2828.2
22.5°	2927.3
25°	2983.0
27.5°	2952.0
30°	2815.8
32.5°	2577.5
35°	2209.4
37.5°	1701.9
40°	1216.1
42.5°	906.7
45°	733.4
47.5°	618.9
50°	516.7
52.5°	411.5
55°	306.3
57.5°	210.4
60°	129.9
62.5°	71.2
65°	34.0
67.5°	15.5
70°	9.3
72.5°	6.2
75°	6.2
77.5°	3.1
80°	3.1
82.5°	3.1
85°	3.1
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)