

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584535

Luminaire Tested: **HCC8S40D010MW-HM82555830-81WDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584535  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S40D010MW-HM82555830-81WDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4806.4 lumens  
Efficiency: N/A  
Efficacy: 117.2 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584535  
CATALOG NUMBER: HCC8S40D010MW-HM82555830-81WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P584535  
 CATALOG NUMBER: HCC8S40D010MW-HM82555830-81WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	110039
5°	107559
10°	104260
15°	102151
20°	101235
25°	99721
30°	94461
35°	78484
40°	46220
45°	30570
50°	24063
55°	17709
60°	12298
65°	7493
70°	3273
75°	1442
80°	1083
85°	0



TEST NUMBER: P584535  
 CATALOG NUMBER: HCC8S40D010MW-HM82555830-81WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	327.2	6.8
10°-20°	904.6	18.8
20°-30°	1340.3	27.9
30°-40°	1238.5	25.8
40°-50°	571.0	11.9
50°-60°	300.4	6.2
60°-70°	106.2	2.2
70°-80°	16.7	0.3
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2572.1	53.5
0°-40°	3810.6	79.3
0°-60°	4682.0	97.4
0°-90°	4806.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4806.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3568	
5°	3475	327
15°	3200	905
25°	2931	1340
35°	2085	1238
45°	701	571
55°	329	300
65°	103	106
75°	12	17
85°	0	2
90°	0	



TEST NUMBER: P584535  
CATALOG NUMBER: HCC8S40D010MW-HM82555830-81WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3568.5
2.5°	3538.2
5°	3474.8
7.5°	3405.3
10°	3329.7
12.5°	3257.3
15°	3199.8
17.5°	3148.5
20°	3085.0
22.5°	3015.5
25°	2930.9
27.5°	2816.0
30°	2652.9
32.5°	2420.2
35°	2084.9
37.5°	1601.4
40°	1148.2
42.5°	861.1
45°	701.0
47.5°	595.2
50°	501.6
52.5°	410.9
55°	329.4
57.5°	259.9
60°	199.4
62.5°	151.1
65°	102.7
67.5°	60.5
70°	36.3
72.5°	21.2
75°	12.1
77.5°	9.0
80°	6.1
82.5°	3.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)