

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584552

Luminaire Tested: **HCC8W40D010MB-HM82555835-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584552
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W40D010MB-HM82555835-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5094.8 lumens
Efficiency: N/A
Efficacy: 124.3 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584552
CATALOG NUMBER: HCC8W40D010MB-HM82555835-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P584552

CATALOG NUMBER: HCC8W40D010MB-HM82555835-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68			
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116645
5°	114013
10°	110516
15°	108283
20°	107309
25°	105710
30°	100130
35°	83190
40°	48993
45°	32402
50°	25507
55°	18768
60°	13031
65°	7946
70°	3462
75°	1537
80°	1137
85°	0



TEST NUMBER: P584552
 CATALOG NUMBER: HCC8W40D010MB-HM82555835-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	346.8	6.8
10°-20°	958.9	18.8
20°-30°	1420.7	27.9
30°-40°	1312.8	25.8
40°-50°	605.3	11.9
50°-60°	318.3	6.2
60°-70°	112.5	2.2
70°-80°	17.7	0.3
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2726.5	53.5
0°-40°	4039.3	79.3
0°-60°	4962.9	97.4
0°-90°	5094.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5094.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3783	
5°	3683	347
15°	3392	959
25°	3107	1421
35°	2210	1313
45°	743	605
55°	349	318
65°	109	112
75°	13	18
85°	0	2
90°	0	



TEST NUMBER: P584552
CATALOG NUMBER: HCC8W40D010MB-HM82555835-81WDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3782.7
2.5°	3750.5
5°	3683.3
7.5°	3609.6
10°	3529.5
12.5°	3452.7
15°	3391.9
17.5°	3337.4
20°	3270.1
22.5°	3196.5
25°	3106.9
27.5°	2985.1
30°	2812.1
32.5°	2565.5
35°	2209.9
37.5°	1697.5
40°	1217.1
42.5°	912.8
45°	743.0
47.5°	630.9
50°	531.7
52.5°	435.5
55°	349.1
57.5°	275.5
60°	211.3
62.5°	160.2
65°	108.9
67.5°	64.0
70°	38.4
72.5°	22.4
75°	12.9
77.5°	9.6
80°	6.4
82.5°	3.2
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)