

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584543

Luminaire Tested: **HCC8S40D010BZ-HM82555835-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584543
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S40D010BZ-HM82555835-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4742.6 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584543
CATALOG NUMBER: HCC8S40D010BZ-HM82555835-81MDW

Luminous Intensity Polar Plot





TEST NUMBER: P584543
 CATALOG NUMBER: HCC8S40D010BZ-HM82555835-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	98	89	83	78	95	88	82	78	85	80	76		83	78	75		80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	69		76	72	68		74	70	67	65
5	86	76	68	63	84	75	68	63	73	67	62		71	66	62		69	65	61	59
6	81	70	63	58	79	69	62	57	67	61	57		66	61	56		64	60	56	54
7	76	65	58	53	74	64	57	53	63	57	52		62	56	52		60	55	52	50
8	72	61	54	49	70	60	53	49	59	53	48		58	52	48		57	52	48	46
9	68	57	50	45	67	56	50	45	55	49	45		54	49	45		53	48	45	43
10	64	53	46	42	63	53	46	42	52	46	42		51	46	42		50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121270
5°	117966
10°	111004
15°	105097
20°	101097
25°	97193
30°	86321
35°	54976
40°	30682
45°	25699
50°	23200
55°	21865
60°	19945
65°	17993
70°	15877
75°	14118
80°	12502
85°	11322



TEST NUMBER: P584543
 CATALOG NUMBER: HCC8S40D010BZ-HM82555835-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	355.3	7.5
10°-20°	928.5	19.6
20°-30°	1295.3	27.3
30°-40°	932.0	19.7
40°-50°	461.9	9.7
50°-60°	361.4	7.6
60°-70°	244.6	5.2
70°-80°	127.0	2.7
80°-90°	36.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2579.0	54.4
0°-40°	3511.0	74.0
0°-60°	4334.3	91.4
0°-90°	4742.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4742.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3933	
5°	3811	355
15°	3292	928
25°	2857	1295
35°	1460	932
45°	589	462
55°	407	361
65°	247	245
75°	118	127
85°	32	37
90°	0	



TEST NUMBER: P584543
CATALOG NUMBER: HCC8S40D010BZ-HM82555835-81MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3932.7
2.5°	3897.5
5°	3811.0
7.5°	3689.2
10°	3545.1
12.5°	3410.7
15°	3292.1
17.5°	3180.0
20°	3080.8
22.5°	2981.5
25°	2856.6
27.5°	2677.3
30°	2424.3
32.5°	2027.2
35°	1460.4
37.5°	996.0
40°	762.2
42.5°	656.5
45°	589.3
47.5°	531.6
50°	483.6
52.5°	442.0
55°	406.7
57.5°	365.1
60°	323.4
62.5°	281.8
65°	246.6
67.5°	211.3
70°	176.1
72.5°	147.3
75°	118.5
77.5°	92.8
80°	70.4
82.5°	51.3
85°	32.0
87.5°	16.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)