

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584571

Luminaire Tested: **HCC8W40D010BZ-HM82555840-81WDWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584571
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W40D010BZ-HM82555840-81WDWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5712.4 lumens
Efficiency: N/A
Efficacy: 139.3 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584571
CATALOG NUMBER: HCC8W40D010BZ-HM82555840-81WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P584571
 CATALOG NUMBER: HCC8W40D010BZ-HM82555840-81WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	103	109	106	103	101	102	100	98		98	97	95		95	93	92	90
2	105	99	94	89	102	97	92	88	93	90	86		90	87	84		88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81	77	74	73
4	92	82	75	70	90	81	75	70	79	73	69		77	72	68		75	71	67	65
5	86	75	68	63	84	74	68	63	73	67	62		71	66	62		69	65	61	59
6	80	69	62	57	79	69	62	57	67	61	56		65	60	56		64	59	56	54
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		59	55	51	49
8	71	59	52	47	69	59	52	47	58	51	47		56	51	47		55	50	47	45
9	67	55	48	43	65	55	48	43	54	47	43		53	47	43		52	47	43	41
10	63	51	45	40	62	51	44	40	50	44	40		49	44	40		48	43	40	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100320
5°	99632
10°	99372
15°	101978
20°	110404
25°	118360
30°	115718
35°	96358
40°	59197
45°	40993
50°	31278
55°	20510
60°	12834
65°	9624
70°	9701
75°	11164
80°	12324
85°	11039



TEST NUMBER: P584571
 CATALOG NUMBER: HCC8W40D010BZ-HM82555840-81WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	305.8	5.4
10°-20°	917.0	16.1
20°-30°	1578.6	27.6
30°-40°	1529.4	26.8
40°-50°	753.3	13.2
50°-60°	355.5	6.2
60°-70°	140.1	2.5
70°-80°	96.7	1.7
80°-90°	35.9	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2801.4	49.0
0°-40°	4330.9	75.8
0°-60°	5439.7	95.2
0°-90°	5712.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5712.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3253	
5°	3219	306
15°	3194	917
25°	3479	1579
35°	2560	1529
45°	940	753
55°	382	356
65°	132	140
75°	94	97
85°	31	36
90°	0	



TEST NUMBER: P584571
CATALOG NUMBER: HCC8W40D010BZ-HM82555840-81WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3253.3
2.5°	3243.0
5°	3218.7
7.5°	3194.4
10°	3173.6
12.5°	3170.0
15°	3194.4
17.5°	3267.3
20°	3364.4
22.5°	3451.0
25°	3478.7
27.5°	3416.4
30°	3249.9
32.5°	2975.8
35°	2559.7
37.5°	1987.4
40°	1470.6
42.5°	1141.1
45°	940.0
47.5°	790.8
50°	652.0
52.5°	513.4
55°	381.5
57.5°	277.5
60°	208.1
62.5°	163.0
65°	131.9
67.5°	114.5
70°	107.6
72.5°	100.6
75°	93.7
77.5°	83.3
80°	69.4
82.5°	52.0
85°	31.2
87.5°	13.9
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)