

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593723

Luminaire Tested: **HCC8W40D010SL-HM82555850-81NDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593723
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W40D010SL-HM82555850-81NDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4696.1 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593723
CATALOG NUMBER: HCC8W40D010SL-HM82555850-81NDH

Luminous Intensity Polar Plot





TEST NUMBER: P593723

CATALOG NUMBER: HCC8W40D010SL-HM82555850-81NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75
6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72
7	88	80	74	70	87	79	74	70	78	73	70	77	73	70	76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	373665
5°	316571
10°	229689
15°	172489
20°	136098
25°	109775
30°	81351
35°	32957
40°	13900
45°	7453
50°	3344
55°	1688
60°	1079
65°	766
70°	631
75°	417
80°	622
85°	1238



TEST NUMBER: P593723
 CATALOG NUMBER: HCC8W40D010SL-HM82555850-81NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	878.1	18.7
10°-20°	1517.5	32.3
20°-30°	1467.2	31.2
30°-40°	644.4	13.7
40°-50°	139.3	3.0
50°-60°	31.3	0.7
60°-70°	10.8	0.2
70°-80°	4.2	0.1
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3862.8	82.3
0°-40°	4507.2	96.0
0°-60°	4677.8	99.6
0°-90°	4696.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4696.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12118	
5°	10227	878
15°	5403	1518
25°	3226	1467
35°	876	644
45°	171	139
55°	31	31
65°	10	11
75°	4	4
85°	4	3
90°	0	



TEST NUMBER: P593723

CATALOG NUMBER: HCC8W40D010SL-HM82555850-81NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	12117.7
1°	12027.0
2°	11779.3
3°	11332.8
4°	10799.1
5°	10227.1
6°	9602.8
7°	8974.9
8°	8385.5
9°	7837.8
10°	7335.5
11°	6861.1
12°	6435.5
13°	6048.4
14°	5706.5
15°	5403.1
17.5°	4722.9
20°	4147.4
22.5°	3641.6
25°	3226.4
27.5°	2804.5
30°	2284.7
32.5°	1552.2
35°	875.5
37.5°	516.2
40°	345.3
42.5°	244.2
45°	170.9
47.5°	111.6
50°	69.7
52.5°	41.9
55°	31.4
57.5°	24.4
60°	17.5
62.5°	13.9
65°	10.5
67.5°	7.0
70°	7.0
72.5°	3.5
75°	3.5
77.5°	3.5
80°	3.5
82.5°	3.5

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P593723
CATALOG NUMBER: HCC8W40D010SL-HM82555850-81NDH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



85°	3.5
87.5°	3.5

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)