

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593730

Luminaire Tested: **HCC8S40D010SL-HM82555850-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593730
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S40D010SL-HM82555850-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5157.3 lumens
Efficiency: N/A
Efficacy: 125.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593730
CATALOG NUMBER: HCC8S40D010SL-HM82555850-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P593730
 CATALOG NUMBER: HCC8S40D010SL-HM82555850-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91		89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81		79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73		71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66		64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60		58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55		53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51		49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47		45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44		42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41		39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121057
5°	119483
10°	115106
15°	110604
20°	107549
25°	104311
30°	93603
35°	61356
40°	33926
45°	28285
50°	25785
55°	24612
60°	22881
65°	20751
70°	18762
75°	16942
80°	15414
85°	14718



TEST NUMBER: P593730
 CATALOG NUMBER: HCC8S40D010SL-HM82555850-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	362.7	7.0
10°-20°	977.5	19.0
20°-30°	1391.1	27.0
30°-40°	1029.5	20.0
40°-50°	509.9	9.9
50°-60°	407.0	7.9
60°-70°	282.5	5.5
70°-80°	152.3	3.0
80°-90°	44.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2731.2	53.0
0°-40°	3760.8	72.9
0°-60°	4677.7	90.7
0°-90°	5157.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5157.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3926	
5°	3860	363
15°	3465	977
25°	3066	1391
35°	1630	1030
45°	649	510
55°	458	407
65°	284	283
75°	142	152
85°	42	45
90°	0	



TEST NUMBER: P593730
CATALOG NUMBER: HCC8S40D010SL-HM82555850-81PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3925.8
2.5°	3908.6
5°	3860.0
7.5°	3783.6
10°	3676.1
12.5°	3565.1
15°	3464.6
17.5°	3367.5
20°	3277.4
22.5°	3187.2
25°	3065.8
27.5°	2888.8
30°	2628.8
32.5°	2229.9
35°	1629.9
37.5°	1113.2
40°	842.8
42.5°	721.4
45°	648.6
47.5°	589.5
50°	537.5
52.5°	492.4
55°	457.8
57.5°	416.1
60°	371.0
62.5°	325.9
65°	284.4
67.5°	242.8
70°	208.1
72.5°	173.4
75°	142.2
77.5°	114.5
80°	86.8
82.5°	62.5
85°	41.6
87.5°	17.4
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)