

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584579

Luminaire Tested: **HCC8S40D010BZ-HM82555927-81NDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584579
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S40D010BZ-HM82555927-81NDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3377.4 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584579
CATALOG NUMBER: HCC8S40D010BZ-HM82555927-81NDH

Luminous Intensity Polar Plot





TEST NUMBER: P584579

CATALOG NUMBER: HCC8S40D010BZ-HM82555927-81NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	92	91	89
3	104	99	94	91	102	97	93	90	95	91	88		92	90	87		90	88	86	84
4	100	93	88	84	98	92	87	84	90	86	83		88	85	82		86	83	81	80
5	96	88	83	79	94	87	82	79	86	81	78		84	80	77		82	79	77	75
6	92	84	78	75	90	83	78	74	81	77	74		80	76	73		79	76	73	72
7	88	80	74	70	87	79	74	70	78	73	70		77	73	70		76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	66		73	69	66		72	69	66	65
9	81	72	67	64	80	72	67	63	71	66	63		70	66	63		69	66	63	62
10	78	69	64	61	77	69	64	61	68	63	60		67	63	60		67	63	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	268742
5°	227680
10°	165193
15°	124054
20°	97878
25°	78953
30°	58509
35°	23701
40°	9999
45°	5360
50°	2408
55°	1215
60°	771
65°	547
70°	451
75°	298
80°	444
85°	885



TEST NUMBER: P584579
 CATALOG NUMBER: HCC8S40D010BZ-HM82555927-81NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	631.5	18.7
10°-20°	1091.4	32.3
20°-30°	1055.2	31.2
30°-40°	463.5	13.7
40°-50°	100.2	3.0
50°-60°	22.5	0.7
60°-70°	7.7	0.2
70°-80°	3.0	0.1
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2778.2	82.3
0°-40°	3241.6	96.0
0°-60°	3364.3	99.6
0°-90°	3377.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3377.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8715	
5°	7355	632
15°	3886	1091
25°	2320	1055
35°	630	463
45°	123	100
55°	23	23
65°	8	8
75°	2	3
85°	2	2
90°	0	



TEST NUMBER: P584579
CATALOG NUMBER: HCC8S40D010BZ-HM82555927-81NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	8715.1
1°	8649.9
2°	8471.7
3°	8150.5
4°	7766.8
5°	7355.4
6°	6906.3
7°	6454.8
8°	6030.8
9°	5636.9
10°	5275.7
11°	4934.6
12°	4628.5
13°	4350.0
14°	4104.2
15°	3885.9
17.5°	3396.7
20°	2982.7
22.5°	2619.1
25°	2320.5
27.5°	2016.9
30°	1643.2
32.5°	1116.3
35°	629.6
37.5°	371.3
40°	248.4
42.5°	175.6
45°	122.9
47.5°	80.3
50°	50.2
52.5°	30.1
55°	22.6
57.5°	17.6
60°	12.5
62.5°	10.0
65°	7.5
67.5°	5.0
70°	5.0
72.5°	2.5
75°	2.5
77.5°	2.5
80°	2.5
82.5°	2.5

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P584579
CATALOG NUMBER: HCC8S40D010BZ-HM82555927-81NDH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



85°	2.5
87.5°	2.5

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)