

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584577

Luminaire Tested: **HCC8S40D010MB-HM82555927-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584577
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S40D010MB-HM82555927-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3694.3 lumens
Efficiency: N/A
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584577
CATALOG NUMBER: HCC8S40D010MB-HM82555927-81MDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584577

CATALOG NUMBER: HCC8S40D010MB-HM82555927-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90		
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80		
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72		
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65		
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59		
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54		
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50		
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46		
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43		
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	94461
5°	91887
10°	86465
15°	81863
20°	78750
25°	75710
30°	67240
35°	42820
40°	23899
45°	20017
50°	18067
55°	17032
60°	15535
65°	14017
70°	12370
75°	10997
80°	9749
85°	8845



TEST NUMBER: P584577
 CATALOG NUMBER: HCC8S40D010MB-HM82555927-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.7	7.5
10°-20°	723.2	19.6
20°-30°	1009.0	27.3
30°-40°	726.0	19.7
40°-50°	359.8	9.7
50°-60°	281.5	7.6
60°-70°	190.6	5.2
70°-80°	99.0	2.7
80°-90°	28.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2008.9	54.4
0°-40°	2734.9	74.0
0°-60°	3376.1	91.4
0°-90°	3694.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3694.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3063	
5°	2968	277
15°	2564	723
25°	2225	1009
35°	1138	726
45°	459	360
55°	317	281
65°	192	191
75°	92	99
85°	25	29
90°	0	



TEST NUMBER: P584577
CATALOG NUMBER: HCC8S40D010MB-HM82555927-81MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3063.3
2.5°	3035.8
5°	2968.5
7.5°	2873.7
10°	2761.4
12.5°	2656.7
15°	2564.3
17.5°	2477.1
20°	2399.8
22.5°	2322.4
25°	2225.2
27.5°	2085.5
30°	1888.4
32.5°	1579.0
35°	1137.5
37.5°	775.8
40°	593.7
42.5°	511.3
45°	459.0
47.5°	414.1
50°	376.6
52.5°	344.3
55°	316.8
57.5°	284.4
60°	251.9
62.5°	219.6
65°	192.1
67.5°	164.7
70°	137.2
72.5°	114.7
75°	92.3
77.5°	72.4
80°	54.9
82.5°	39.9
85°	25.0
87.5°	12.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)