

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584581

Luminaire Tested: **HCC8S40D010SL-HM82555927-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584581
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S40D010SL-HM82555927-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3709.2 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584581
CATALOG NUMBER: HCC8S40D010SL-HM82555927-81PSMDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P584581

CATALOG NUMBER: HCC8S40D010SL-HM82555927-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|-----|---|--|---|
| RF | 20 | | | | | 20 | | | | | 20 | | | | | 20 | | | | | 20 | | | | | |
| RC | 80 | | | | | 70 | | | | | 50 | | | | | 30 | | | | | 10 | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | 100 | | | |
| 1 | 111 | 108 | 105 | 102 | 109 | 106 | 103 | 100 | 101 | 99 | 97 | 98 | 96 | 94 | 94 | 93 | 91 | 89 | | | | | 89 | | | |
| 2 | 104 | 98 | 92 | 88 | 102 | 96 | 91 | 87 | 92 | 88 | 85 | 89 | 86 | 83 | 86 | 84 | 81 | 79 | | | | | 79 | | | |
| 3 | 97 | 89 | 83 | 77 | 95 | 87 | 82 | 77 | 85 | 80 | 76 | 82 | 78 | 74 | 80 | 76 | 73 | 71 | | | | | 71 | | | |
| 4 | 91 | 81 | 74 | 69 | 89 | 80 | 74 | 69 | 78 | 72 | 68 | 76 | 71 | 67 | 74 | 70 | 66 | 64 | | | | | 64 | | | |
| 5 | 85 | 75 | 68 | 62 | 83 | 74 | 67 | 62 | 72 | 66 | 61 | 70 | 65 | 61 | 68 | 64 | 60 | 58 | | | | | 58 | | | |
| 6 | 80 | 69 | 62 | 57 | 78 | 68 | 61 | 56 | 67 | 61 | 56 | 65 | 60 | 56 | 64 | 59 | 55 | 53 | | | | | 53 | | | |
| 7 | 75 | 64 | 57 | 52 | 74 | 63 | 57 | 52 | 62 | 56 | 51 | 61 | 55 | 51 | 60 | 55 | 51 | 49 | | | | | 49 | | | |
| 8 | 71 | 60 | 53 | 48 | 70 | 59 | 52 | 48 | 58 | 52 | 47 | 57 | 51 | 47 | 56 | 51 | 47 | 45 | | | | | 45 | | | |
| 9 | 67 | 56 | 49 | 44 | 66 | 55 | 49 | 44 | 54 | 48 | 44 | 53 | 48 | 44 | 52 | 47 | 44 | 42 | | | | | 42 | | | |
| 10 | 64 | 52 | 46 | 41 | 62 | 52 | 45 | 41 | 51 | 45 | 41 | 50 | 45 | 41 | 49 | 44 | 41 | 39 | | | | | 39 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 87066 |
| 5° | 85929 |
| 10° | 82786 |
| 15° | 79545 |
| 20° | 77346 |
| 25° | 75023 |
| 30° | 67322 |
| 35° | 44130 |
| 40° | 24398 |
| 45° | 20344 |
| 50° | 18546 |
| 55° | 17704 |
| 60° | 16460 |
| 65° | 14929 |
| 70° | 13497 |
| 75° | 12176 |
| 80° | 11081 |
| 85° | 10614 |



TEST NUMBER: P584581
 CATALOG NUMBER: HCC8S40D010SL-HM82555927-81PSMDW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 260.8 | 7.0 |
| 10°-20° | 703.0 | 19.0 |
| 20°-30° | 1000.5 | 27.0 |
| 30°-40° | 740.5 | 20.0 |
| 40°-50° | 366.8 | 9.9 |
| 50°-60° | 292.7 | 7.9 |
| 60°-70° | 203.2 | 5.5 |
| 70°-80° | 109.5 | 3.0 |
| 80°-90° | 32.3 | 0.9 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1964.3 | 53.0 |
| 0°-40° | 2704.8 | 72.9 |
| 0°-60° | 3364.2 | 90.7 |
| 0°-90° | 3709.2 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 3709.2 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2824 | |
| 5° | 2776 | 261 |
| 15° | 2492 | 703 |
| 25° | 2205 | 1000 |
| 35° | 1172 | 740 |
| 45° | 466 | 367 |
| 55° | 329 | 293 |
| 65° | 205 | 203 |
| 75° | 102 | 109 |
| 85° | 30 | 32 |
| 90° | 0 | |



TEST NUMBER: P584581
CATALOG NUMBER: HCC8S40D010SL-HM82555927-81PSMDW

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 2823.5 |
| 2.5° | 2811.0 |
| 5° | 2776.0 |
| 7.5° | 2721.2 |
| 10° | 2643.9 |
| 12.5° | 2564.1 |
| 15° | 2491.7 |
| 17.5° | 2421.9 |
| 20° | 2357.0 |
| 22.5° | 2292.2 |
| 25° | 2205.0 |
| 27.5° | 2077.7 |
| 30° | 1890.7 |
| 32.5° | 1603.8 |
| 35° | 1172.3 |
| 37.5° | 800.6 |
| 40° | 606.1 |
| 42.5° | 518.8 |
| 45° | 466.5 |
| 47.5° | 424.0 |
| 50° | 386.6 |
| 52.5° | 354.1 |
| 55° | 329.3 |
| 57.5° | 299.3 |
| 60° | 266.9 |
| 62.5° | 234.4 |
| 65° | 204.6 |
| 67.5° | 174.6 |
| 70° | 149.7 |
| 72.5° | 124.7 |
| 75° | 102.2 |
| 77.5° | 82.3 |
| 80° | 62.4 |
| 82.5° | 44.9 |
| 85° | 30.0 |
| 87.5° | 12.5 |
| 90° | 0.0 |

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)