

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584587

Luminaire Tested: **HCC8W40D010SL-HM82555927-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584587
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W40D010SL-HM82555927-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3831.4 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584587
CATALOG NUMBER: HCC8W40D010SL-HM82555927-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P584587

CATALOG NUMBER: HCC8W40D010SL-HM82555927-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	76597
5°	76503
10°	75750
15°	74840
20°	74149
25°	73319
30°	69177
35°	56331
40°	31120
45°	20775
50°	18426
55°	17300
60°	17071
65°	16921
70°	15291
75°	13666
80°	11969
85°	10579



TEST NUMBER: P584587
 CATALOG NUMBER: HCC8W40D010SL-HM82555927-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.2	6.1
10°-20°	661.9	17.3
20°-30°	983.6	25.7
30°-40°	885.8	23.1
40°-50°	392.7	10.2
50°-60°	290.8	7.6
60°-70°	226.2	5.9
70°-80°	122.6	3.2
80°-90°	33.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1879.8	49.1
0°-40°	2765.5	72.2
0°-60°	3449.1	90.0
0°-90°	3831.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3831.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2484	
5°	2472	234
15°	2344	662
25°	2155	984
35°	1496	886
45°	476	393
55°	322	291
65°	232	226
75°	115	123
85°	30	34
90°	0	



TEST NUMBER: P584587
CATALOG NUMBER: HCC8W40D010SL-HM82555927-81WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2484.0
2.5°	2479.0
5°	2471.5
7.5°	2451.6
10°	2419.2
12.5°	2381.8
15°	2344.3
17.5°	2306.9
20°	2259.6
22.5°	2212.2
25°	2154.9
27.5°	2067.5
30°	1942.8
32.5°	1763.2
35°	1496.4
37.5°	1117.3
40°	773.1
42.5°	571.1
45°	476.4
47.5°	421.5
50°	384.1
52.5°	349.1
55°	321.8
57.5°	299.3
60°	276.8
62.5°	256.9
65°	231.9
67.5°	202.1
70°	169.6
72.5°	142.2
75°	114.7
77.5°	89.7
80°	67.4
82.5°	47.4
85°	29.9
87.5°	12.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)