

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584605

Luminaire Tested: **HCC8W40D010MW-HM82555930-81WDWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584605
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W40D010MW-HM82555930-81WDWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4892.2 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584605
CATALOG NUMBER: HCC8W40D010MW-HM82555930-81WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P584605
 CATALOG NUMBER: HCC8W40D010MW-HM82555930-81WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			90	
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81			81	
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73			73	
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65	
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59			59	
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54			54	
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49			49	
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45			45	
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41			41	
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85919
5°	85325
10°	85106
15°	87338
20°	94551
25°	101368
30°	99104
35°	82524
40°	50700
45°	35105
50°	26793
55°	17569
60°	10996
65°	8238
70°	8304
75°	9555
80°	10548
85°	9482



TEST NUMBER: P584605
 CATALOG NUMBER: HCC8W40D010MW-HM82555930-81WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.9	5.4
10°-20°	785.4	16.1
20°-30°	1352.0	27.6
30°-40°	1309.9	26.8
40°-50°	645.2	13.2
50°-60°	304.5	6.2
60°-70°	120.0	2.5
70°-80°	82.8	1.7
80°-90°	30.7	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2399.2	49.0
0°-40°	3709.1	75.8
0°-60°	4658.7	95.2
0°-90°	4892.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4892.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2786	
5°	2756	262
15°	2736	785
25°	2979	1352
35°	2192	1310
45°	805	645
55°	327	304
65°	113	120
75°	80	83
85°	27	31
90°	0	



TEST NUMBER: P584605
CATALOG NUMBER: HCC8W40D010MW-HM82555930-81WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2786.3
2.5°	2777.3
5°	2756.5
7.5°	2735.8
10°	2718.0
12.5°	2715.0
15°	2735.8
17.5°	2798.2
20°	2881.3
22.5°	2955.6
25°	2979.3
27.5°	2925.9
30°	2783.3
32.5°	2548.6
35°	2192.2
37.5°	1702.1
40°	1259.5
42.5°	977.2
45°	805.0
47.5°	677.2
50°	558.5
52.5°	439.6
55°	326.8
57.5°	237.6
60°	178.3
62.5°	139.6
65°	112.9
67.5°	98.1
70°	92.1
72.5°	86.2
75°	80.2
77.5°	71.3
80°	59.4
82.5°	44.5
85°	26.8
87.5°	11.9
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)