

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584631

Luminaire Tested: **HCC8W40D010MB-HM82555940-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584631
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W40D010MB-HM82555940-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4420.0 lumens
Efficiency: N/A
Efficacy: 107.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584631
CATALOG NUMBER: HCC8W40D010MB-HM82555940-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P584631

CATALOG NUMBER: HCC8W40D010MB-HM82555940-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	110169
5°	109878
10°	108045
15°	106470
20°	103913
25°	98643
30°	81361
35°	41890
40°	28045
45°	24046
50°	20753
55°	18107
60°	16084
65°	14454
70°	13100
75°	11795
80°	10548
85°	10543



TEST NUMBER: P584631
 CATALOG NUMBER: HCC8W40D010MB-HM82555940-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	335.6	7.6
10°-20°	938.3	21.2
20°-30°	1300.1	29.4
30°-40°	780.9	17.7
40°-50°	427.5	9.7
50°-60°	303.7	6.9
60°-70°	197.2	4.5
70°-80°	105.3	2.4
80°-90°	31.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2574.0	58.2
0°-40°	3354.9	75.9
0°-60°	4086.0	92.4
0°-90°	4420.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4420.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3573	
5°	3550	336
15°	3335	938
25°	2899	1300
35°	1113	781
45°	551	427
55°	337	304
65°	198	197
75°	99	105
85°	30	31
90°	0	



TEST NUMBER: P584631
CATALOG NUMBER: HCC8W40D010MB-HM82555940-81NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3572.7
2.5°	3566.2
5°	3549.7
7.5°	3510.0
10°	3450.6
12.5°	3394.5
15°	3335.1
17.5°	3259.1
20°	3166.6
22.5°	3054.4
25°	2899.2
27.5°	2654.8
30°	2285.0
32.5°	1674.1
35°	1112.8
37.5°	822.2
40°	696.7
42.5°	617.5
45°	551.4
47.5°	488.7
50°	432.6
52.5°	379.7
55°	336.8
57.5°	297.1
60°	260.8
62.5°	227.9
65°	198.1
67.5°	168.4
70°	145.3
72.5°	118.9
75°	99.0
77.5°	79.3
80°	59.4
82.5°	43.0
85°	29.8
87.5°	13.2
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)