

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593740

Luminaire Tested: **HCC8W40D010MB-HM82555950-81NDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593740
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W40D010MB-HM82555950-81NDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4469.5 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593740
CATALOG NUMBER: HCC8W40D010MB-HM82555950-81NDH

Luminous Intensity Polar Plot





TEST NUMBER: P593740

CATALOG NUMBER: HCC8W40D010MB-HM82555950-81NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89			
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84			
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80			
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75			
6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72			
7	88	80	74	70	87	79	74	70	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65			
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62			
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	355638
5°	301298
10°	218608
15°	164170
20°	129529
25°	104481
30°	77427
35°	31365
40°	13231
45°	7095
50°	3185
55°	1607
60°	1018
65°	730
70°	604
75°	393
80°	586
85°	1168



TEST NUMBER: P593740
 CATALOG NUMBER: HCC8W40D010MB-HM82555950-81NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	835.7	18.7
10°-20°	1444.3	32.3
20°-30°	1396.4	31.2
30°-40°	613.3	13.7
40°-50°	132.6	3.0
50°-60°	29.8	0.7
60°-70°	10.3	0.2
70°-80°	3.9	0.1
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3676.5	82.3
0°-40°	4289.8	96.0
0°-60°	4452.2	99.6
0°-90°	4469.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4469.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11533	
5°	9734	836
15°	5142	1444
25°	3071	1396
35°	833	613
45°	163	133
55°	30	30
65°	10	10
75°	3	4
85°	3	3
90°	0	



TEST NUMBER: P593740
CATALOG NUMBER: HCC8W40D010MB-HM82555950-81NDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	11533.1
1°	11446.8
2°	11211.1
3°	10786.2
4°	10278.3
5°	9733.7
6°	9139.6
7°	8541.9
8°	7980.9
9°	7459.6
10°	6981.6
11°	6530.1
12°	6125.0
13°	5756.6
14°	5431.3
15°	5142.5
17.5°	4495.1
20°	3947.2
22.5°	3465.9
25°	3070.8
27.5°	2669.2
30°	2174.5
32.5°	1477.4
35°	833.2
37.5°	491.4
40°	328.7
42.5°	232.4
45°	162.7
47.5°	106.3
50°	66.4
52.5°	39.9
55°	29.9
57.5°	23.2
60°	16.5
62.5°	13.3
65°	10.0
67.5°	6.7
70°	6.7
72.5°	3.3
75°	3.3
77.5°	3.3
80°	3.3
82.5°	3.3

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P593740
CATALOG NUMBER: HCC8W40D010MB-HM82555950-81NDH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



85°	3.3
87.5°	3.3

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)