

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593741

Luminaire Tested: **HCC8W40D010MB-HM82555950-81WDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593741  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W40D010MB-HM82555950-81WDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5251.8 lumens  
Efficiency: N/A  
Efficacy: 128.1 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593741  
CATALOG NUMBER: HCC8W40D010MB-HM82555950-81WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P593741  
 CATALOG NUMBER: HCC8W40D010MB-HM82555950-81WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93		92
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85		83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77		75
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70		68
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64		62
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58		57
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54		52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49		48
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46		44
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42		41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	120237
5°	117527
10°	113923
15°	111616
20°	110617
25°	108962
30°	103213
35°	85753
40°	50503
45°	33405
50°	26294
55°	19349
60°	13438
65°	8187
70°	3570
75°	1573
80°	1154
85°	0



TEST NUMBER: P593741  
 CATALOG NUMBER: HCC8W40D010MB-HM82555950-81WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	357.5	6.8
10°-20°	988.5	18.8
20°-30°	1464.5	27.9
30°-40°	1353.2	25.8
40°-50°	624.0	11.9
50°-60°	328.2	6.2
60°-70°	116.0	2.2
70°-80°	18.2	0.3
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2810.5	53.5
0°-40°	4163.7	79.3
0°-60°	5115.9	97.4
0°-90°	5251.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5251.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3899	
5°	3797	358
15°	3496	988
25°	3202	1464
35°	2278	1353
45°	766	624
55°	360	328
65°	112	116
75°	13	18
85°	0	2
90°	0	



TEST NUMBER: P593741  
CATALOG NUMBER: HCC8W40D010MB-HM82555950-81WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3899.2
2.5°	3866.1
5°	3796.8
7.5°	3720.9
10°	3638.3
12.5°	3559.1
15°	3496.3
17.5°	3440.2
20°	3370.9
22.5°	3295.0
25°	3202.5
27.5°	3077.1
30°	2898.7
32.5°	2644.5
35°	2278.0
37.5°	1749.8
40°	1254.6
42.5°	940.9
45°	766.0
47.5°	650.5
50°	548.1
52.5°	449.0
55°	359.9
57.5°	283.9
60°	217.9
62.5°	165.1
65°	112.2
67.5°	66.0
70°	39.6
72.5°	23.1
75°	13.2
77.5°	9.9
80°	6.5
82.5°	3.3
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)