

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584666

Luminaire Tested: **HCC8W45D010MB-HM82555830-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584666
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W45D010MB-HM82555830-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4782.0 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584666
CATALOG NUMBER: HCC8W45D010MB-HM82555830-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P584666
 CATALOG NUMBER: HCC8W45D010MB-HM82555830-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89				
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79				
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71				
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64				
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58				
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53				
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49				
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45				
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42				
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	112250
5°	110788
10°	106730
15°	102556
20°	99719
25°	96717
30°	86791
35°	56895
40°	31458
45°	26222
50°	23910
55°	22822
60°	21215
65°	19241
70°	17401
75°	15703
80°	14277
85°	13657



TEST NUMBER: P584666
 CATALOG NUMBER: HCC8W45D010MB-HM82555830-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	336.3	7.0
10°-20°	906.3	19.0
20°-30°	1289.9	27.0
30°-40°	954.6	20.0
40°-50°	472.8	9.9
50°-60°	377.4	7.9
60°-70°	262.0	5.5
70°-80°	141.2	3.0
80°-90°	41.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2532.5	53.0
0°-40°	3487.1	72.9
0°-60°	4337.3	90.7
0°-90°	4782.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4782.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3640	
5°	3579	336
15°	3212	906
25°	2843	1290
35°	1511	955
45°	601	473
55°	424	377
65°	264	262
75°	132	141
85°	39	42
90°	0	



TEST NUMBER: P584666
CATALOG NUMBER: HCC8W45D010MB-HM82555830-81PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3640.2
2.5°	3624.1
5°	3579.1
7.5°	3508.3
10°	3408.6
12.5°	3305.7
15°	3212.5
17.5°	3122.4
20°	3038.8
22.5°	2955.3
25°	2842.6
27.5°	2678.7
30°	2437.5
32.5°	2067.6
35°	1511.4
37.5°	1032.2
40°	781.5
42.5°	668.8
45°	601.3
47.5°	546.6
50°	498.4
52.5°	456.6
55°	424.5
57.5°	385.9
60°	344.0
62.5°	302.3
65°	263.7
67.5°	225.1
70°	193.0
72.5°	160.8
75°	131.8
77.5°	106.2
80°	80.4
82.5°	57.8
85°	38.6
87.5°	16.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)