

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584662

Luminaire Tested: **HCC8W45D010SL-HM82555830-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584662
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W45D010SL-HM82555830-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4762.7 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584662
CATALOG NUMBER: HCC8W45D010SL-HM82555830-81MDW

Luminous Intensity Polar Plot





TEST NUMBER: P584662
 CATALOG NUMBER: HCC8W45D010SL-HM82555830-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121785
5°	118464
10°	111477
15°	105544
20°	101527
25°	97605
30°	86688
35°	55205
40°	30810
45°	25808
50°	23296
55°	21956
60°	20031
65°	18066
70°	15949
75°	14166
80°	12555
85°	11357



TEST NUMBER: P584662
 CATALOG NUMBER: HCC8W45D010SL-HM82555830-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	356.8	7.5
10°-20°	932.4	19.6
20°-30°	1300.8	27.3
30°-40°	936.0	19.7
40°-50°	463.8	9.7
50°-60°	362.9	7.6
60°-70°	245.7	5.2
70°-80°	127.6	2.7
80°-90°	36.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2590.0	54.4
0°-40°	3525.9	74.0
0°-60°	4352.7	91.4
0°-90°	4762.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4762.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3949	
5°	3827	357
15°	3306	932
25°	2869	1301
35°	1466	936
45°	592	464
55°	408	363
65°	248	246
75°	119	128
85°	32	37
90°	0	



TEST NUMBER: P584662
CATALOG NUMBER: HCC8W45D010SL-HM82555830-81MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3949.4
2.5°	3913.9
5°	3827.1
7.5°	3704.9
10°	3560.2
12.5°	3425.2
15°	3306.1
17.5°	3193.6
20°	3093.9
22.5°	2994.2
25°	2868.7
27.5°	2688.6
30°	2434.6
32.5°	2035.7
35°	1466.5
37.5°	1000.2
40°	765.4
42.5°	659.3
45°	591.8
47.5°	533.8
50°	485.6
52.5°	443.9
55°	408.4
57.5°	366.7
60°	324.8
62.5°	283.0
65°	247.6
67.5°	212.3
70°	176.9
72.5°	147.9
75°	118.9
77.5°	93.3
80°	70.7
82.5°	51.5
85°	32.1
87.5°	16.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)