

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584686

Luminaire Tested: **HCC8W45D010MB-HM82555835-81WDBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584686  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W45D010MB-HM82555835-81WDBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5106.5 lumens  
Efficiency: N/A  
Efficacy: 116.1 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 44  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584686  
CATALOG NUMBER: HCC8W45D010MB-HM82555835-81WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P584686  
 CATALOG NUMBER: HCC8W45D010MB-HM82555835-81WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	95676
5°	94884
10°	93629
15°	94700
20°	102266
25°	111834
30°	110477
35°	91641
40°	53940
45°	35241
50°	27316
55°	18150
60°	8832
65°	2736
70°	920
75°	810
80°	604
85°	1203



TEST NUMBER: P584686  
 CATALOG NUMBER: HCC8W45D010MB-HM82555835-81WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	290.3	5.7
10°-20°	852.2	16.7
20°-30°	1490.0	29.2
30°-40°	1449.4	28.4
40°-50°	659.2	12.9
50°-60°	305.6	6.0
60°-70°	51.2	1.0
70°-80°	6.3	0.1
80°-90°	2.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2632.5	51.6
0°-40°	4081.9	79.9
0°-60°	5046.7	98.8
0°-90°	5106.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5106.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3103	
5°	3065	290
15°	2966	852
25°	3287	1490
35°	2434	1449
45°	808	659
55°	338	306
65°	38	51
75°	7	6
85°	3	2
90°	0	



TEST NUMBER: P584686  
CATALOG NUMBER: HCC8W45D010MB-HM82555835-81WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3102.7
2.5°	3095.9
5°	3065.3
7.5°	3031.1
10°	2990.2
12.5°	2959.6
15°	2966.4
17.5°	3020.9
20°	3116.4
22.5°	3225.5
25°	3286.9
27.5°	3252.7
30°	3102.7
32.5°	2840.2
35°	2434.4
37.5°	1875.3
40°	1340.0
42.5°	999.0
45°	808.1
47.5°	682.0
50°	569.4
52.5°	453.5
55°	337.6
57.5°	231.9
60°	143.2
62.5°	78.5
65°	37.5
67.5°	17.0
70°	10.2
72.5°	6.8
75°	6.8
77.5°	3.4
80°	3.4
82.5°	3.4
85°	3.4
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)