

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584713

Luminaire Tested: **HCC8W45D010SL-HM82555927-81MDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584713  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W45D010SL-HM82555927-81MDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3932.5 lumens  
Efficiency: N/A  
Efficacy: 89.4 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.95  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 44  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584713  
CATALOG NUMBER: HCC8W45D010SL-HM82555927-81MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P584713  
 CATALOG NUMBER: HCC8W45D010SL-HM82555927-81MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	100554
5°	97812
10°	92042
15°	87146
20°	83830
25°	80590
30°	71577
35°	45583
40°	25440
45°	21307
50°	19232
55°	18128
60°	16534
65°	14921
70°	13163
75°	11712
80°	10371
85°	9376



TEST NUMBER: P584713  
 CATALOG NUMBER: HCC8W45D010SL-HM82555927-81MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	294.6	7.5
10°-20°	769.9	19.6
20°-30°	1074.0	27.3
30°-40°	772.8	19.7
40°-50°	383.0	9.7
50°-60°	299.6	7.6
60°-70°	202.8	5.2
70°-80°	105.4	2.7
80°-90°	30.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2138.5	54.4
0°-40°	2911.3	74.0
0°-60°	3593.9	91.4
0°-90°	3932.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3932.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3261	
5°	3160	295
15°	2730	770
25°	2369	1074
35°	1211	773
45°	489	383
55°	337	300
65°	204	203
75°	98	105
85°	26	30
90°	0	



TEST NUMBER: P584713  
CATALOG NUMBER: HCC8W45D010SL-HM82555927-81MDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3260.9
2.5°	3231.7
5°	3159.9
7.5°	3059.1
10°	2939.5
12.5°	2828.1
15°	2729.8
17.5°	2636.9
20°	2554.6
22.5°	2472.2
25°	2368.6
27.5°	2220.0
30°	2010.2
32.5°	1680.9
35°	1210.9
37.5°	825.8
40°	632.0
42.5°	544.4
45°	488.6
47.5°	440.8
50°	400.9
52.5°	366.4
55°	337.2
57.5°	302.8
60°	268.1
62.5°	233.7
65°	204.5
67.5°	175.2
70°	146.0
72.5°	122.1
75°	98.3
77.5°	77.1
80°	58.4
82.5°	42.5
85°	26.5
87.5°	13.3
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)